

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275569

Luminaire Tested: P3AS05R609835DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609835DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 463.0 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275569

CATALOG NUMBER: P3AS05R609835DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1275569

CATALOG NUMBER: P3AS05R609835DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121306
5°	114528
10°	111554
15°	108990
20°	101345
25°	90586
30°	69201
35°	39940
40°	15515
45°	6450
50°	1433
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6450 cd/sqm

TEST NUMBER: P1275569

CATALOG NUMBER: P3AS05R609835DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	10.6
10°-20°	133.7	28.9
20°-30°	167.5	36.2
30°-40°	93.6	20.2
40°-50°	17.8	3.8
50°-60°	0.9	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	350.4	75.7
0°-40°	444.0	95.9
0°-60°	462.7	99.9
0°-90°	463.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	463.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	553	
5°	520	49
15°	480	134
25°	374	168
35°	149	94
45°	21	18
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1275569

CATALOG NUMBER: P3AS05R609835DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	553.2
1°	551.0
2°	543.8
3°	535.2
4°	527.3
5°	520.3
6°	515.0
7°	510.4
8°	507.0
9°	503.8
10°	501.0
11°	498.1
12°	494.9
13°	490.9
14°	486.2
15°	480.1
16°	472.7
17°	464.4
18°	454.9
19°	444.1
20°	434.3
21°	423.7
22°	412.7
23°	401.1
24°	388.5
25°	374.4
26°	358.0
27°	339.6
28°	318.9
29°	297.0
30°	273.3
31°	249.4
32°	224.8
32.5°	211.4
33°	199.2
34°	174.1
35°	149.2
36°	126.9
37°	103.2
37.5°	92.4
38°	81.8
39°	65.9
40°	54.2
42.5°	33.0
45°	20.8

TEST NUMBER: P1275569

CATALOG NUMBER: P3AS05R609835DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	11.6
50°	4.2
52.5°	0.9
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)