

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275581

Luminaire Tested: P3AS05R609835DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609835DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 319.0 lumens
Efficiency: N/A
Efficacy: 44.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275581

CATALOG NUMBER: P3AS05R609835DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1275581

CATALOG NUMBER: P3AS05R609835DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56618
5°	55998
10°	54063
15°	51056
20°	47067
25°	42631
30°	37829
35°	32337
40°	25705
45°	18141
50°	10814
55°	5467
60°	5263
65°	4825
70°	4488
75°	4236
80°	3915
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18141 cd/sqm

TEST NUMBER: P1275581

CATALOG NUMBER: P3AS05R609835DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.9	7.5
10°-20°	62.9	19.7
20°-30°	80.7	25.3
30°-40°	74.8	23.5
40°-50°	45.6	14.3
50°-60°	15.2	4.8
60°-70°	9.2	2.9
70°-80°	5.2	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.5	52.5
0°-40°	242.3	76.0
0°-60°	303.1	95.0
0°-90°	319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	319.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	258	
5°	254	24
15°	225	63
25°	176	81
35°	121	75
45°	58	46
55°	14	15
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1275581

CATALOG NUMBER: P3AS05R609835DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	258.2
2.5°	257.1
5°	254.4
7.5°	249.3
10°	242.8
12.5°	234.6
15°	224.9
17.5°	213.7
20°	201.7
22.5°	188.9
25°	176.2
27.5°	163.0
30°	149.4
32.5°	135.9
35°	120.8
37.5°	104.9
40°	89.8
42.5°	73.9
45°	58.5
47.5°	45.3
50°	31.7
52.5°	19.0
55°	14.3
57.5°	13.2
60°	12.0
62.5°	10.5
65°	9.3
67.5°	8.1
70°	7.0
72.5°	5.8
75°	5.0
77.5°	3.9
80°	3.1
82.5°	1.9
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)