

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275582

Luminaire Tested: P3AS05R609835DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1275582  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R609835DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 138.0 lumens  
Efficiency: N/A  
Efficacy: 19.2 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275582  
CATALOG NUMBER: P3AS05R609835DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1275582  
 CATALOG NUMBER: P3AS05R609835DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34975
5°	34184
10°	32019
15°	28718
20°	24689
25°	20421
30°	16129
35°	11993
40°	8244
45°	5179
50°	2831
55°	1682
60°	1491
65°	1297
70°	1090
75°	1101
80°	1010
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5179 cd/sqm



TEST NUMBER: P1275582  
 CATALOG NUMBER: P3AS05R609835DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	14.5	10.5
10°-20°	35.1	25.5
20°-30°	38.5	27.9
30°-40°	28.1	20.3
40°-50°	13.3	9.6
50°-60°	4.3	3.2
60°-70°	2.5	1.8
70°-80°	1.3	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	88.1	63.9
0°-40°	116.2	84.2
0°-60°	133.8	97.0
0°-90°	138.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	138.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	160	
5°	155	14
15°	126	35
25°	84	39
35°	45	28
45°	17	13
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1275582  
CATALOG NUMBER: P3AS05R609835DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	159.5
2.5°	158.5
5°	155.3
7.5°	150.4
10°	143.8
12.5°	135.8
15°	126.5
17.5°	116.4
20°	105.8
22.5°	95.0
25°	84.4
27.5°	73.8
30°	63.7
32.5°	54.0
35°	44.8
37.5°	36.4
40°	28.8
42.5°	22.2
45°	16.7
47.5°	12.1
50°	8.3
52.5°	5.5
55°	4.4
57.5°	3.8
60°	3.4
62.5°	2.8
65°	2.5
67.5°	2.1
70°	1.7
72.5°	1.5
75°	1.3
77.5°	0.9
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)