

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274736

Luminaire Tested: P3AS20R359830D010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274736  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R359830D010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 786.9 lumens  
Efficiency: N/A  
Efficacy: 28.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274736  
CATALOG NUMBER: P3AS20R359830D010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1274736  
 CATALOG NUMBER: P3AS20R359830D010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	72	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	69	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	396920
5°	381465
10°	332370
15°	254576
20°	170325
25°	103070
30°	59148
35°	33060
40°	17576
45°	9055
50°	4332
55°	3441
60°	3289
65°	2698
70°	2885
75°	2542
80°	2778
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9055 cd/sqm



TEST NUMBER: P1274736  
 CATALOG NUMBER: P3AS20R359830D010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.7	20.0
10°-20°	305.6	38.8
20°-30°	200.1	25.4
30°-40°	81.1	10.3
40°-50°	24.4	3.1
50°-60°	8.3	1.0
60°-70°	5.5	0.7
70°-80°	3.2	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.3	84.3
0°-40°	744.4	94.6
0°-60°	777.1	98.7
0°-90°	786.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1810	
5°	1733	158
15°	1121	306
25°	426	200
35°	124	81
45°	29	24
55°	9	8
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1274736  
CATALOG NUMBER: P3AS20R359830D010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1810.1
1°	1807.1
2°	1798.9
3°	1782.4
4°	1763.0
5°	1733.0
6°	1695.6
7°	1653.7
8°	1606.5
9°	1552.6
10°	1492.7
11°	1426.1
12°	1356.5
13°	1278.6
14°	1204.5
15°	1121.4
17.5°	920.0
20°	729.9
22.5°	561.5
25°	426.0
27.5°	317.4
30°	233.6
32.5°	171.4
35°	123.5
37.5°	87.6
40°	61.4
42.5°	42.7
45°	29.2
47.5°	19.5
50°	12.7
52.5°	9.7
55°	9.0
57.5°	8.2
60°	7.5
62.5°	6.7
65°	5.2
67.5°	4.5
70°	4.5
72.5°	3.7
75°	3.0
77.5°	2.2
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7



TEST NUMBER: P1274736  
CATALOG NUMBER: P3AS20R359830D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)