

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274744

Luminaire Tested: P3AS20R359830D010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359830D010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1236.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274744

CATALOG NUMBER: P3AS20R359830D010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1274744

CATALOG NUMBER: P3AS20R359830D010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	282346
5°	276359
10°	258802
15°	232306
20°	202084
25°	172220
30°	144250
35°	114894
40°	83070
45°	52564
50°	28656
55°	19842
60°	18770
65°	17434
70°	16669
75°	14234
80°	13512
85°	11573

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 52564 cd/sqm

TEST NUMBER: P1274744

CATALOG NUMBER: P3AS20R359830D010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	9.5
10°-20°	284.8	23.0
20°-30°	326.4	26.4
30°-40°	266.3	21.5
40°-50°	134.3	10.9
50°-60°	49.9	4.0
60°-70°	33.4	2.7
70°-80°	18.5	1.5
80°-90°	5.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.0	58.9
0°-40°	994.3	80.4
0°-60°	1178.4	95.3
0°-90°	1236.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1236.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1288	
5°	1256	117
15°	1023	285
25°	712	326
35°	429	266
45°	170	134
55°	52	50
65°	34	33
75°	17	19
85°	5	6
90°	0	

TEST NUMBER: P1274744

CATALOG NUMBER: P3AS20R359830D010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1287.6
1°	1286.0
2°	1283.0
3°	1276.9
4°	1267.7
5°	1255.5
6°	1240.2
7°	1224.9
8°	1205.1
9°	1185.2
10°	1162.3
11°	1137.9
12°	1111.9
13°	1082.9
14°	1052.4
15°	1023.3
17.5°	945.4
20°	866.0
22.5°	785.1
25°	711.8
27.5°	640.0
30°	569.7
32.5°	499.4
35°	429.2
37.5°	358.9
40°	290.2
42.5°	226.1
45°	169.5
47.5°	122.2
50°	84.0
52.5°	61.1
55°	51.9
57.5°	47.3
60°	42.8
62.5°	38.2
65°	33.6
67.5°	29.0
70°	26.0
72.5°	21.4
75°	16.8
77.5°	13.7
80°	10.7
82.5°	7.6
85°	4.6
87.5°	3.1



TEST NUMBER: P1274744
CATALOG NUMBER: P3AS20R359830D010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)