

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275662

Luminaire Tested: P3AS09R159835DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159835DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 450.1 lumens
Efficiency: N/A
Efficacy: 40.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275662
CATALOG NUMBER: P3AS09R159835DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1275662
 CATALOG NUMBER: P3AS09R159835DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91	91	91	91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65	65	65	65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60	60	60	60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56	56	56	56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113500
5°	110433
10°	100911
15°	88400
20°	75817
25°	63318
30°	50666
35°	37986
40°	27566
45°	18017
50°	11292
55°	7646
60°	6754
65°	6226
70°	5834
75°	5338
80°	5051
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18017 cd/sqm



TEST NUMBER: P1275662
 CATALOG NUMBER: P3AS09R159835DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.3	10.3
10°-20°	108.5	24.1
20°-30°	119.5	26.6
30°-40°	89.5	19.9
40°-50°	46.4	10.3
50°-60°	19.3	4.3
60°-70°	11.9	2.7
70°-80°	6.7	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.3	61.0
0°-40°	363.8	80.8
0°-60°	429.5	95.4
0°-90°	450.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	450.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	502	46
15°	389	108
25°	262	120
35°	142	90
45°	58	46
55°	20	19
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1275662
CATALOG NUMBER: P3AS09R159835DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	517.6
1°	518.2
2°	516.5
3°	513.1
4°	507.9
5°	501.7
6°	493.7
7°	485.1
8°	474.9
9°	464.0
10°	453.2
12.5°	421.9
15°	389.4
17.5°	356.9
20°	324.9
22.5°	292.5
25°	261.7
27.5°	230.9
30°	200.1
32.5°	169.9
35°	141.9
37.5°	118.0
40°	96.3
42.5°	76.4
45°	58.1
47.5°	43.9
50°	33.1
52.5°	24.5
55°	20.0
57.5°	17.7
60°	15.4
62.5°	13.7
65°	12.0
67.5°	10.3
70°	9.1
72.5°	7.4
75°	6.3
77.5°	5.1
80°	4.0
82.5°	2.9
85°	1.7
87.5°	0.6
90°	0.0

(END OF REPORT)