

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275688

Luminaire Tested: P3AS09R209835DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209835DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 591.0 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275688

CATALOG NUMBER: P3AS09R209835DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1275688

CATALOG NUMBER: P3AS09R209835DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	454700
5°	413338
10°	305494
15°	188968
20°	107926
25°	61600
30°	34562
35°	18792
40°	10305
45°	5675
50°	3309
55°	2409
60°	2237
65°	2075
70°	1859
75°	1949
80°	1389
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5675 cd/sqm

TEST NUMBER: P1275688

CATALOG NUMBER: P3AS09R209835DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.6	27.5
10°-20°	232.1	39.3
20°-30°	121.2	20.5
30°-40°	46.9	7.9
40°-50°	15.2	2.6
50°-60°	6.0	1.0
60°-70°	4.0	0.7
70°-80°	2.3	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.9	87.3
0°-40°	562.8	95.2
0°-60°	583.9	98.8
0°-90°	591.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	591.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2074	
5°	1878	163
15°	832	232
25°	255	121
35°	70	47
45°	18	15
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1275688

CATALOG NUMBER: P3AS09R209835DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2073.6
1°	2069.6
2°	2045.1
3°	2007.4
4°	1949.2
5°	1877.8
6°	1793.3
7°	1699.7
8°	1591.2
9°	1485.6
10°	1372.0
12.5°	1090.5
15°	832.4
17.5°	622.9
20°	462.5
22.5°	342.6
25°	254.6
27.5°	187.8
30°	136.5
32.5°	98.8
35°	70.2
37.5°	50.8
40°	36.0
42.5°	25.7
45°	18.3
47.5°	13.1
50°	9.7
52.5°	7.4
55°	6.3
57.5°	5.7
60°	5.1
62.5°	4.6
65°	4.0
67.5°	3.4
70°	2.9
72.5°	2.9
75°	2.3
77.5°	1.7
80°	1.1
82.5°	1.1
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)