

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274775

Luminaire Tested: P3AS20R409830D010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1274775  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R409830D010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1365.1 lumens  
Efficiency: N/A  
Efficacy: 49.8 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274775

CATALOG NUMBER: P3AS20R409830D010 E3DLD1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1274775

CATALOG NUMBER: P3AS20R409830D010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 89  |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 83  |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  |  | 80  | 75  | 72  |  | 78  |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  |  | 75  | 70  | 66  |  | 73  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 61  |  | 70  | 65  | 61  |  | 68  |
| 7   | 79  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 57  |  | 65  | 60  | 57  |  | 64  |
| 8   | 75  | 64  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 53  |  | 62  | 56  | 53  |  | 61  |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  |  | 58  | 53  | 49  |  | 57  |
| 10  | 67  | 57  | 51  | 46  | 66  | 56  | 50  | 46  | 56  | 50  | 46  |  | 55  | 50  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 306423 |
| 5°  | 300858 |
| 10° | 283606 |
| 15° | 257595 |
| 20° | 226306 |
| 25° | 193245 |
| 30° | 160075 |
| 35° | 123460 |
| 40° | 87879  |
| 45° | 59200  |
| 50° | 32306  |
| 55° | 22785  |
| 60° | 21446  |
| 65° | 19821  |
| 70° | 17631  |
| 75° | 16860  |
| 80° | 13512  |
| 85° | 11573  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 59200 cd/sqm

TEST NUMBER: P1274775

CATALOG NUMBER: P3AS20R409830D010 E3DLD1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 127.5  | 9.3       |
| 10°-20°   | 316.1  | 23.2      |
| 20°-30°   | 365.4  | 26.8      |
| 30°-40°   | 288.0  | 21.1      |
| 40°-50°   | 147.8  | 10.8      |
| 50°-60°   | 56.5   | 4.1       |
| 60°-70°   | 37.4   | 2.7       |
| 70°-80°   | 20.4   | 1.5       |
| 80°-90°   | 6.1    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 808.9  | 59.3      |
| 0°-40°    | 1096.9 | 80.4      |
| 0°-60°    | 1301.3 | 95.3      |
| 0°-90°    | 1365.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1365.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1397 |      |
| 5°  | 1367 | 127  |
| 15° | 1135 | 316  |
| 25° | 799  | 365  |
| 35° | 461  | 288  |
| 45° | 191  | 148  |
| 55° | 60   | 57   |
| 65° | 38   | 37   |
| 75° | 20   | 20   |
| 85° | 5    | 6    |
| 90° | 0    |      |

TEST NUMBER: P1274775

CATALOG NUMBER: P3AS20R409830D010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1397.4 |
| 2.5°  | 1389.7 |
| 5°    | 1366.8 |
| 7.5°  | 1327.1 |
| 10°   | 1273.7 |
| 12.5° | 1211.0 |
| 15°   | 1134.7 |
| 17.5° | 1055.3 |
| 20°   | 969.8  |
| 22.5° | 882.7  |
| 25°   | 798.7  |
| 27.5° | 714.7  |
| 30°   | 632.2  |
| 32.5° | 548.3  |
| 35°   | 461.2  |
| 37.5° | 380.3  |
| 40°   | 307.0  |
| 42.5° | 244.3  |
| 45°   | 190.9  |
| 47.5° | 139.0  |
| 50°   | 94.7   |
| 52.5° | 68.7   |
| 55°   | 59.6   |
| 57.5° | 53.5   |
| 60°   | 48.9   |
| 62.5° | 42.8   |
| 65°   | 38.2   |
| 67.5° | 32.1   |
| 70°   | 27.5   |
| 72.5° | 22.9   |
| 75°   | 19.9   |
| 77.5° | 15.3   |
| 80°   | 10.7   |
| 82.5° | 9.2    |
| 85°   | 4.6    |
| 87.5° | 3.1    |
| 90°   | 0.0    |

(END OF REPORT)