

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275751

Luminaire Tested: P3AS09R309835DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309835DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 465.1 lumens
Efficiency: N/A
Efficacy: 42.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275751

CATALOG NUMBER: P3AS09R309835DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1275751

CATALOG NUMBER: P3AS09R309835DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109860
5°	107396
10°	99865
15°	88854
20°	76423
25°	64746
30°	53755
35°	42162
40°	30228
45°	19816
50°	11292
55°	7417
60°	7017
65°	6538
70°	5834
75°	5338
80°	5051
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19816 cd/sqm

TEST NUMBER: P1275751

CATALOG NUMBER: P3AS09R309835DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.3	9.7
10°-20°	108.8	23.4
20°-30°	122.6	26.4
30°-40°	97.9	21.1
40°-50°	50.3	10.8
50°-60°	18.9	4.1
60°-70°	12.4	2.7
70°-80°	6.7	1.4
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.7	59.5
0°-40°	374.7	80.6
0°-60°	444.0	95.5
0°-90°	465.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	501	
5°	488	45
15°	391	109
25°	268	123
35°	158	98
45°	64	50
55°	19	19
65°	13	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1275751

CATALOG NUMBER: P3AS09R309835DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	501.0
1°	501.0
2°	499.3
3°	496.4
4°	492.4
5°	487.9
6°	482.2
7°	474.7
8°	466.8
9°	457.6
10°	448.5
11°	438.2
12°	427.4
13°	416.0
14°	404.0
15°	391.4
17.5°	359.5
20°	327.5
22.5°	296.7
25°	267.6
27.5°	239.1
30°	212.3
32.5°	184.9
35°	157.5
37.5°	130.7
40°	105.6
42.5°	83.3
45°	63.9
47.5°	47.4
50°	33.1
52.5°	23.4
55°	19.4
57.5°	17.7
60°	16.0
62.5°	14.3
65°	12.6
67.5°	10.8
70°	9.1
72.5°	7.4
75°	6.3
77.5°	5.1
80°	4.0
82.5°	2.9
85°	1.7
87.5°	0.6



TEST NUMBER: P1275751

CATALOG NUMBER: P3AS09R309835DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)