

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274810

Luminaire Tested: P3AS20R459830D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459830D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1102.0 lumens
Efficiency: N/A
Efficacy: 40.2 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274810

CATALOG NUMBER: P3AS20R459830D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1274810

CATALOG NUMBER: P3AS20R459830D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	328241
5°	320756
10°	295897
15°	257300
20°	211372
25°	164453
30°	121436
35°	85447
40°	53328
45°	28902
50°	15624
55°	13419
60°	12060
65°	10325
70°	8784
75°	9065
80°	7703
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28902 cd/sqm

TEST NUMBER: P1274810

CATALOG NUMBER: P3AS20R459830D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.0	12.2
10°-20°	313.3	28.4
20°-30°	311.1	28.2
30°-40°	200.3	18.2
40°-50°	77.2	7.0
50°-60°	31.4	2.8
60°-70°	19.8	1.8
70°-80°	10.7	1.0
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	759.3	68.9
0°-40°	959.6	87.1
0°-60°	1068.1	96.9
0°-90°	1102.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1102.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1497	
5°	1457	135
15°	1133	313
25°	680	311
35°	319	200
45°	93	77
55°	35	31
65°	20	20
75°	11	11
85°	3	3
90°	0	

TEST NUMBER: P1274810

CATALOG NUMBER: P3AS20R459830D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1496.9
2.5°	1489.3
5°	1457.2
7.5°	1402.2
10°	1328.9
12.5°	1237.2
15°	1133.4
17.5°	1020.3
20°	905.8
22.5°	789.7
25°	679.7
27.5°	575.9
30°	479.6
32.5°	395.6
35°	319.2
37.5°	250.5
40°	186.3
42.5°	134.4
45°	93.2
47.5°	62.6
50°	45.8
52.5°	38.2
55°	35.1
57.5°	30.5
60°	27.5
62.5°	22.9
65°	19.9
67.5°	16.8
70°	13.7
72.5°	12.2
75°	10.7
77.5°	7.6
80°	6.1
82.5°	4.6
85°	3.1
87.5°	1.5
90°	0.0

(END OF REPORT)