

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275780

Luminaire Tested: P3AS09R359835DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359835DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 462.0 lumens
Efficiency: N/A
Efficacy: 42.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275780
CATALOG NUMBER: P3AS09R359835DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1275780
 CATALOG NUMBER: P3AS09R359835DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105540
5°	103302
10°	96747
15°	86834
20°	75537
25°	64359
30°	53907
35°	42938
40°	31058
45°	19661
50°	10712
55°	7417
60°	7017
65°	6538
70°	6219
75°	5338
80°	5051
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19661 cd/sqm



TEST NUMBER: P1275780
 CATALOG NUMBER: P3AS09R359835DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.7	9.5
10°-20°	106.4	23.0
20°-30°	122.0	26.4
30°-40°	99.5	21.5
40°-50°	50.2	10.9
50°-60°	18.6	4.0
60°-70°	12.5	2.7
70°-80°	6.9	1.5
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.1	58.9
0°-40°	371.6	80.4
0°-60°	440.5	95.3
0°-90°	462.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	462.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	481	
5°	469	44
15°	382	106
25°	266	122
35°	160	100
45°	63	50
55°	19	19
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1275780
CATALOG NUMBER: P3AS09R359835DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	481.3
1°	480.7
2°	479.6
3°	477.3
4°	473.9
5°	469.3
6°	463.6
7°	457.9
8°	450.4
9°	443.0
10°	434.5
11°	425.3
12°	415.6
13°	404.8
14°	393.4
15°	382.5
17.5°	353.4
20°	323.7
22.5°	293.4
25°	266.0
27.5°	239.2
30°	212.9
32.5°	186.7
35°	160.4
37.5°	134.2
40°	108.5
42.5°	84.5
45°	63.4
47.5°	45.7
50°	31.4
52.5°	22.8
55°	19.4
57.5°	17.7
60°	16.0
62.5°	14.3
65°	12.6
67.5°	10.8
70°	9.7
72.5°	8.0
75°	6.3
77.5°	5.1
80°	4.0
82.5°	2.9
85°	1.7
87.5°	1.1



TEST NUMBER: P1275780
CATALOG NUMBER: P3AS09R359835DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)