

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275820

Luminaire Tested: P3AS09R409835DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409835DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 419.0 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275820

CATALOG NUMBER: P3AS09R409835DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1275820

CATALOG NUMBER: P3AS09R409835DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130472
5°	127823
10°	119014
15°	103724
20°	83587
25°	62665
30°	44057
35°	28857
40°	17461
45°	10451
50°	6243
55°	5008
60°	4517
65°	3840
70°	3654
75°	2881
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10451 cd/sqm

TEST NUMBER: P1275820

CATALOG NUMBER: P3AS09R409835DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	12.9
10°-20°	125.8	30.0
20°-30°	118.6	28.3
30°-40°	68.6	16.4
40°-50°	27.3	6.5
50°-60°	12.1	2.9
60°-70°	7.5	1.8
70°-80°	3.9	0.9
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.4	71.2
0°-40°	366.9	87.6
0°-60°	406.4	97.0
0°-90°	419.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	419.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	595	
5°	581	54
15°	457	126
25°	259	119
35°	108	69
45°	34	27
55°	13	12
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1275820

CATALOG NUMBER: P3AS09R409835DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	595.0
2.5°	591.6
5°	580.7
7.5°	560.7
10°	534.5
12.5°	499.1
15°	456.9
17.5°	409.6
20°	358.2
22.5°	306.9
25°	259.0
27.5°	214.5
30°	174.0
32.5°	138.6
35°	107.8
37.5°	81.6
40°	61.0
42.5°	45.6
45°	33.7
47.5°	24.5
50°	18.3
52.5°	14.8
55°	13.1
57.5°	12.0
60°	10.3
62.5°	8.6
65°	7.4
67.5°	6.3
70°	5.7
72.5°	4.6
75°	3.4
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)