

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275830

Luminaire Tested: P3AS09R459835DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459835DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 638.0 lumens
Efficiency: N/A
Efficacy: 58.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275830

CATALOG NUMBER: P3AS09R459835DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1275830

CATALOG NUMBER: P3AS09R459835DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239586
5°	233986
10°	215093
15°	182248
20°	141389
25°	98836
30°	62263
35°	36647
40°	20753
45°	10079
50°	3514
55°	2829
60°	2763
65°	2646
70°	2565
75°	2457
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10079 cd/sqm

TEST NUMBER: P1275830

CATALOG NUMBER: P3AS09R459835DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.4	15.4
10°-20°	220.5	34.6
20°-30°	187.2	29.3
30°-40°	89.3	14.0
40°-50°	26.9	4.2
50°-60°	6.8	1.1
60°-70°	5.1	0.8
70°-80°	3.0	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	506.0	79.3
0°-40°	595.3	93.3
0°-60°	629.1	98.6
0°-90°	638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	638.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1093	
5°	1063	98
15°	803	220
25°	408	187
35°	137	89
45°	32	27
55°	7	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1275830

CATALOG NUMBER: P3AS09R459835DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1092.6
2.5°	1085.8
5°	1063.0
7.5°	1023.6
10°	966.0
12.5°	889.5
15°	802.8
17.5°	706.4
20°	605.9
22.5°	503.8
25°	408.5
27.5°	321.8
30°	245.9
32.5°	184.9
35°	136.9
37.5°	101.0
40°	72.5
42.5°	50.2
45°	32.5
47.5°	18.3
50°	10.3
52.5°	8.0
55°	7.4
57.5°	6.8
60°	6.3
62.5°	5.7
65°	5.1
67.5°	4.6
70°	4.0
72.5°	3.4
75°	2.9
77.5°	2.3
80°	1.7
82.5°	1.1
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)