

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274884

Luminaire Tested: P3AS20R609830D010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1274884  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R609830D010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1111.0 lumens  
Efficiency: N/A  
Efficacy: 40.5 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274884

CATALOG NUMBER: P3AS20R609830D010 E3DL1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1274884

CATALOG NUMBER: P3AS20R609830D010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 96  | 92  | 96  | 93  | 90  |  | 93  | 91  | 88  |  | 91  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 86  | 82  |  | 87  | 84  | 81  |  | 85  |
| 4   | 95  | 87  | 81  | 77  | 93  | 86  | 80  | 76  | 84  | 79  | 75  |  | 82  | 78  | 74  |  | 80  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  |
| 6   | 85  | 76  | 69  | 65  | 84  | 75  | 69  | 65  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  |
| 7   | 81  | 71  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 55  |  | 63  |
| 9   | 73  | 63  | 57  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 60  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  |  | 57  | 52  | 49  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 281556 |
| 5°  | 275236 |
| 10° | 257688 |
| 15° | 231193 |
| 20° | 198794 |
| 25° | 164380 |
| 30° | 129893 |
| 35° | 96450  |
| 40° | 66439  |
| 45° | 41679  |
| 50° | 22925  |
| 55° | 13419  |
| 60° | 12060  |
| 65° | 10273  |
| 70° | 8784   |
| 75° | 9065   |
| 80° | 7703   |
| 85° | 7799   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41679 cd/sqm

TEST NUMBER: P1274884

CATALOG NUMBER: P3AS20R609830D010 E3DL1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 116.4  | 10.5      |
| 10°-20°   | 282.8  | 25.5      |
| 20°-30°   | 310.2  | 27.9      |
| 30°-40°   | 226.0  | 20.3      |
| 40°-50°   | 106.8  | 9.6       |
| 50°-60°   | 35.0   | 3.1       |
| 60°-70°   | 19.8   | 1.8       |
| 70°-80°   | 10.7   | 1.0       |
| 80°-90°   | 3.3    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 709.4  | 63.9      |
| 0°-40°    | 935.4  | 84.2      |
| 0°-60°    | 1077.2 | 97.0      |
| 0°-90°    | 1111.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1111.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1284 |      |
| 5°  | 1250 | 116  |
| 15° | 1018 | 283  |
| 25° | 679  | 310  |
| 35° | 360  | 226  |
| 45° | 134  | 107  |
| 55° | 35   | 35   |
| 65° | 20   | 20   |
| 75° | 11   | 11   |
| 85° | 3    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1274884

CATALOG NUMBER: P3AS20R609830D010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1284.0 |
| 2.5°  | 1276.4 |
| 5°    | 1250.4 |
| 7.5°  | 1210.7 |
| 10°   | 1157.3 |
| 12.5° | 1093.2 |
| 15°   | 1018.4 |
| 17.5° | 937.4  |
| 20°   | 851.9  |
| 22.5° | 764.9  |
| 25°   | 679.4  |
| 27.5° | 593.9  |
| 30°   | 513.0  |
| 32.5° | 435.1  |
| 35°   | 360.3  |
| 37.5° | 293.1  |
| 40°   | 232.1  |
| 42.5° | 178.6  |
| 45°   | 134.4  |
| 47.5° | 97.7   |
| 50°   | 67.2   |
| 52.5° | 44.3   |
| 55°   | 35.1   |
| 57.5° | 30.5   |
| 60°   | 27.5   |
| 62.5° | 22.9   |
| 65°   | 19.8   |
| 67.5° | 16.8   |
| 70°   | 13.7   |
| 72.5° | 12.2   |
| 75°   | 10.7   |
| 77.5° | 7.6    |
| 80°   | 6.1    |
| 82.5° | 4.6    |
| 85°   | 3.1    |
| 87.5° | 1.5    |
| 90°   | 0.0    |

(END OF REPORT)