

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275861

Luminaire Tested: P3AS09R509835DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509835DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 421.0 lumens
Efficiency: N/A
Efficacy: 38.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275861

CATALOG NUMBER: P3AS09R509835DE010 E3DL1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1275861

CATALOG NUMBER: P3AS09R509835DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122446
5°	119150
10°	109862
15°	96618
20°	80834
25°	64117
30°	47045
35°	32337
40°	20553
45°	11474
50°	6209
55°	5238
60°	4517
65°	4151
70°	3654
75°	3389
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11474 cd/sqm

TEST NUMBER: P1275861

CATALOG NUMBER: P3AS09R509835DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.1	11.9
10°-20°	117.9	28.0
20°-30°	120.6	28.6
30°-40°	76.5	18.2
40°-50°	30.4	7.2
50°-60°	12.4	2.9
60°-70°	7.9	1.9
70°-80°	4.1	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.6	68.5
0°-40°	365.1	86.7
0°-60°	407.8	96.9
0°-90°	421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	421.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	558	
5°	541	50
15°	426	118
25°	265	121
35°	121	76
45°	37	30
55°	14	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1275861

CATALOG NUMBER: P3AS09R509835DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	558.4
2.5°	554.4
5°	541.3
7.5°	520.8
10°	493.4
12.5°	461.0
15°	425.6
17.5°	386.9
20°	346.4
22.5°	306.0
25°	265.0
27.5°	223.9
30°	185.8
32.5°	151.6
35°	120.8
37.5°	94.6
40°	71.8
42.5°	53.0
45°	37.0
47.5°	25.1
50°	18.2
52.5°	15.4
55°	13.7
57.5°	12.0
60°	10.3
62.5°	9.1
65°	8.0
67.5°	6.8
70°	5.7
72.5°	4.6
75°	4.0
77.5°	2.8
80°	2.3
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)