

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275867

Luminaire Tested: P3AS09R509835DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509835DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 499.9 lumens
Efficiency: N/A
Efficacy: 45.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275867
CATALOG NUMBER: P3AS09R509835DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1275867

CATALOG NUMBER: P3AS09R509835DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101615
5°	100110
10°	95678
15°	88604
20°	79644
25°	69996
30°	59528
35°	48265
40°	36268
45°	23351
50°	11087
55°	8717
60°	8245
65°	7679
70°	6924
75°	6270
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23351 cd/sqm



TEST NUMBER: P1275867
 CATALOG NUMBER: P3AS09R509835DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.6	8.5
10°-20°	108.8	21.8
20°-30°	132.2	26.4
30°-40°	112.1	22.4
40°-50°	58.2	11.6
50°-60°	21.0	4.2
60°-70°	14.5	2.9
70°-80°	7.9	1.6
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	283.7	56.7
0°-40°	395.8	79.2
0°-60°	475.0	95.0
0°-90°	499.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	463	
5°	455	43
15°	390	109
25°	289	132
35°	180	112
45°	75	58
55°	23	21
65°	15	15
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1275867
CATALOG NUMBER: P3AS09R509835DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	463.4
2.5°	461.7
5°	454.8
7.5°	444.5
10°	429.7
12.5°	410.9
15°	390.3
17.5°	366.9
20°	341.3
22.5°	315.0
25°	289.3
27.5°	262.5
30°	235.1
32.5°	207.7
35°	180.3
37.5°	153.5
40°	126.7
42.5°	101.0
45°	75.3
47.5°	50.2
50°	32.5
52.5°	25.1
55°	22.8
57.5°	20.5
60°	18.8
62.5°	16.5
65°	14.8
67.5°	12.6
70°	10.8
72.5°	9.1
75°	7.4
77.5°	5.7
80°	4.6
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0

(END OF REPORT)