

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274899

Luminaire Tested: P3AS20R659830D010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274899  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R659830D010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1889.0 lumens  
Efficiency: N/A  
Efficacy: 68.9 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274899  
CATALOG NUMBER: P3AS20R659830D010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1274899

CATALOG NUMBER: P3AS20R659830D010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	461630
5°	434469
10°	428961
15°	421387
20°	397845
25°	369263
30°	287032
35°	166050
40°	66897
45°	30794
50°	11974
55°	4664
60°	4035
65°	3943
70°	3911
75°	3897
80°	3915
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30794 cd/sqm



TEST NUMBER: P1274899  
 CATALOG NUMBER: P3AS20R659830D010 E3CB1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.6	9.9
10°-20°	518.3	27.4
20°-30°	678.5	35.9
30°-40°	393.0	20.8
40°-50°	84.1	4.5
50°-60°	13.7	0.7
60°-70°	7.6	0.4
70°-80°	4.5	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1384.5	73.3
0°-40°	1777.5	94.1
0°-60°	1875.3	99.3
0°-90°	1889.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1889.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2105	
5°	1974	188
15°	1856	518
25°	1526	679
35°	620	393
45°	99	84
55°	12	14
65°	8	8
75°	5	4
85°	2	2
90°	0	

TEST NUMBER: P1274899

CATALOG NUMBER: P3AS20R659830D010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2105.2
2.5°	2045.6
5°	1973.8
7.5°	1944.8
10°	1926.5
12.5°	1900.5
15°	1856.2
17.5°	1787.4
20°	1704.9
22.5°	1627.0
25°	1526.2
27.5°	1356.6
30°	1133.6
32.5°	878.4
35°	620.3
37.5°	392.6
40°	233.7
42.5°	146.7
45°	99.3
47.5°	64.2
50°	35.1
52.5°	16.8
55°	12.2
57.5°	10.7
60°	9.2
62.5°	9.2
65°	7.6
67.5°	6.1
70°	6.1
72.5°	4.6
75°	4.6
77.5°	3.1
80°	3.1
82.5°	1.5
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)