

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275887

Luminaire Tested: P3AS09R559835DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559835DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 98CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 622.0 lumens
Efficiency: N/A
Efficacy: 56.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275887
CATALOG NUMBER: P3AS09R559835DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1275887
 CATALOG NUMBER: P3AS09R559835DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	170798
5°	169073
10°	163257
15°	150920
20°	130235
25°	102853
30°	72973
35°	47060
40°	28253
45°	15940
50°	8563
55°	3058
60°	2763
65°	2646
70°	2565
75°	2457
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15940 cd/sqm



TEST NUMBER: P1275887
 CATALOG NUMBER: P3AS09R559835DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	11.6
10°-20°	183.8	29.6
20°-30°	192.6	31.0
30°-40°	112.4	18.1
40°-50°	42.1	6.8
50°-60°	9.9	1.6
60°-70°	5.1	0.8
70°-80°	3.0	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.7	72.1
0°-40°	561.1	90.2
0°-60°	613.1	98.6
0°-90°	622.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	622.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	779	
5°	768	72
15°	665	184
25°	425	193
35°	176	112
45°	51	42
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1275887
CATALOG NUMBER: P3AS09R559835DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	778.9
2.5°	776.6
5°	768.1
7.5°	754.4
10°	733.2
12.5°	703.6
15°	664.8
17.5°	615.7
20°	558.1
22.5°	493.6
25°	425.1
27.5°	354.9
30°	288.2
32.5°	227.7
35°	175.8
37.5°	133.5
40°	98.7
42.5°	70.8
45°	51.4
47.5°	37.1
50°	25.1
52.5°	14.3
55°	8.0
57.5°	6.8
60°	6.3
62.5°	5.7
65°	5.1
67.5°	4.6
70°	4.0
72.5°	3.4
75°	2.9
77.5°	2.3
80°	1.7
82.5°	1.1
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)