

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275905

Luminaire Tested: P3AS09R609835DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609835DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 738.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275905

CATALOG NUMBER: P3AS09R609835DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1275905

CATALOG NUMBER: P3AS09R609835DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176236
5°	169249
10°	174256
15°	176482
20°	155834
25°	131330
30°	106523
35°	69359
40°	31860
45°	12218
50°	4094
55°	1109
60°	1009
65°	882
70°	705
75°	932
80°	758
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12218 cd/sqm

TEST NUMBER: P1275905

CATALOG NUMBER: P3AS09R609835DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.0	10.0
10°-20°	212.9	28.8
20°-30°	248.3	33.6
30°-40°	160.2	21.7
40°-50°	35.9	4.9
50°-60°	3.6	0.5
60°-70°	1.7	0.2
70°-80°	1.0	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.2	72.5
0°-40°	695.4	94.2
0°-60°	734.9	99.6
0°-90°	738.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	738.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	804	
5°	769	74
15°	777	213
25°	543	248
35°	259	160
45°	39	36
55°	3	4
65°	2	2
75°	1	1
85°	1	0
90°	0	

TEST NUMBER: P1275905

CATALOG NUMBER: P3AS09R609835DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	803.7
2.5°	790.5
5°	768.9
7.5°	767.7
10°	782.6
12.5°	792.3
15°	777.4
17.5°	732.9
20°	667.8
22.5°	599.9
25°	542.8
27.5°	486.9
30°	420.7
32.5°	343.0
35°	259.1
37.5°	176.9
40°	111.3
42.5°	66.8
45°	39.4
47.5°	22.8
50°	12.0
52.5°	4.0
55°	2.9
57.5°	2.3
60°	2.3
62.5°	1.7
65°	1.7
67.5°	1.7
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)