

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274944

Luminaire Tested: P3AS20R709830D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709830D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 538.0 lumens
Efficiency: N/A
Efficacy: 19.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274944

CATALOG NUMBER: P3AS20R709830D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274944

CATALOG NUMBER: P3AS20R709830D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126196
5°	123883
10°	116809
15°	106017
20°	92735
25°	78222
30°	64035
35°	49684
40°	35552
45°	22514
50°	11224
55°	6881
60°	5921
65°	5448
70°	4809
75°	4406
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22514 cd/sqm

TEST NUMBER: P1274944

CATALOG NUMBER: P3AS20R709830D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	9.8
10°-20°	129.9	24.2
20°-30°	148.0	27.5
30°-40°	115.7	21.5
40°-50°	56.8	10.6
50°-60°	17.5	3.3
60°-70°	10.4	1.9
70°-80°	5.5	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	330.4	61.4
0°-40°	446.2	82.9
0°-60°	520.5	96.7
0°-90°	538.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	538.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	576	
5°	563	53
15°	467	130
25°	323	148
35°	186	116
45°	73	57
55°	18	17
65°	10	10
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1274944

CATALOG NUMBER: P3AS20R709830D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	575.5
2.5°	572.5
5°	562.8
7.5°	547.1
10°	524.6
12.5°	498.4
15°	467.0
17.5°	433.3
20°	397.4
22.5°	360.0
25°	323.3
27.5°	287.4
30°	252.9
32.5°	218.5
35°	185.6
37.5°	154.2
40°	124.2
42.5°	96.5
45°	72.6
47.5°	50.9
50°	32.9
52.5°	21.7
55°	18.0
57.5°	15.7
60°	13.5
62.5°	12.0
65°	10.5
67.5°	9.0
70°	7.5
72.5°	6.0
75°	5.2
77.5°	4.5
80°	3.0
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)