

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275927

Luminaire Tested: P3AS09R609835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 203.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275927
CATALOG NUMBER: P3AS09R609835DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1275927
 CATALOG NUMBER: P3AS09R609835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51443
5°	50297
10°	47093
15°	42248
20°	36333
25°	30026
30°	23725
35°	17614
40°	12137
45°	7598
50°	4196
55°	2447
60°	2193
65°	1868
70°	1603
75°	1694
80°	1389
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7598 cd/sqm



TEST NUMBER: P1275927
 CATALOG NUMBER: P3AS09R609835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.3	10.5
10°-20°	51.7	25.5
20°-30°	56.7	27.9
30°-40°	41.3	20.3
40°-50°	19.5	9.6
50°-60°	6.4	3.1
60°-70°	3.6	1.8
70°-80°	2.0	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	129.6	63.9
0°-40°	170.9	84.2
0°-60°	196.8	97.0
0°-90°	203.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	203.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	235	
5°	228	21
15°	186	52
25°	124	57
35°	66	41
45°	24	20
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1275927
CATALOG NUMBER: P3AS09R609835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	234.6
2.5°	233.2
5°	228.5
7.5°	221.2
10°	211.5
12.5°	199.7
15°	186.1
17.5°	171.3
20°	155.7
22.5°	139.8
25°	124.1
27.5°	108.5
30°	93.7
32.5°	79.5
35°	65.8
37.5°	53.6
40°	42.4
42.5°	32.6
45°	24.5
47.5°	17.9
50°	12.3
52.5°	8.1
55°	6.4
57.5°	5.6
60°	5.0
62.5°	4.2
65°	3.6
67.5°	3.1
70°	2.5
72.5°	2.2
75°	2.0
77.5°	1.4
80°	1.1
82.5°	0.8
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)