

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275966

Luminaire Tested: P3AS09R709835DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709835DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 714.0 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275966

CATALOG NUMBER: P3AS09R709835DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1275966

CATALOG NUMBER: P3AS09R709835DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141787
5°	135285
10°	128722
15°	125267
20°	120644
25°	114176
30°	106194
35°	89222
40°	57508
45°	26731
50°	6993
55°	1759
60°	1754
65°	1505
70°	1475
75°	1440
80°	1389
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26731 cd/sqm

TEST NUMBER: P1275966

CATALOG NUMBER: P3AS09R709835DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	8.1
10°-20°	155.1	21.7
20°-30°	216.6	30.3
30°-40°	200.9	28.1
40°-50°	72.0	10.1
50°-60°	6.1	0.9
60°-70°	3.1	0.4
70°-80°	2.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.2	60.1
0°-40°	630.1	88.2
0°-60°	708.2	99.2
0°-90°	714.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	714.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	647	
5°	615	58
15°	552	155
25°	472	217
35°	333	201
45°	86	72
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1275966

CATALOG NUMBER: P3AS09R709835DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	646.6
2.5°	636.9
5°	614.6
7.5°	594.1
10°	578.1
12.5°	565.0
15°	551.8
17.5°	535.9
20°	517.0
22.5°	495.3
25°	471.9
27.5°	448.0
30°	419.4
32.5°	382.9
35°	333.3
37.5°	269.9
40°	200.9
42.5°	137.0
45°	86.2
47.5°	47.9
50°	20.5
52.5°	6.8
55°	4.6
57.5°	4.0
60°	4.0
62.5°	3.4
65°	2.9
67.5°	2.9
70°	2.3
72.5°	2.3
75°	1.7
77.5°	1.7
80°	1.1
82.5°	1.1
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)