

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275972

Luminaire Tested: P3AS09R709835DE010 E3D1WMH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1275972  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709835DE010 E3D1WMH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 681.0 lumens  
Efficiency: N/A  
Efficacy: 61.9 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275972  
CATALOG NUMBER: P3AS09R709835DE010 E3D1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1275972  
 CATALOG NUMBER: P3AS09R709835DE010 E3D1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |     |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 95  | 93  |    |    |    | 93  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |    |    |    | 85  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  | 88  | 84  | 81  | 86  | 83  | 80  | 79  |    |    |    | 79  |
| 4   | 95  | 87  | 81  | 77  | 94  | 86  | 81  | 76  | 84  | 79  | 76  | 82  | 78  | 75  | 80  | 77  | 74  | 72  |    |    |    | 72  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  | 77  | 72  | 69  | 75  | 71  | 68  | 66  |    |    |    | 66  |
| 6   | 85  | 75  | 69  | 64  | 83  | 75  | 69  | 64  | 73  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 63  | 61  |    |    |    | 61  |
| 7   | 80  | 70  | 64  | 59  | 79  | 70  | 63  | 59  | 68  | 63  | 59  | 67  | 62  | 58  | 66  | 61  | 58  | 57  |    |    |    | 57  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 52  |    |    |    | 52  |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 50  | 49  |    |    |    | 49  |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 55  | 50  | 47  | 45  |    |    |    | 45  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 132424 |
| 5°  | 124851 |
| 10° | 118390 |
| 15° | 116255 |
| 20° | 112056 |
| 25° | 105635 |
| 30° | 104877 |
| 35° | 91337  |
| 40° | 59082  |
| 45° | 27941  |
| 50° | 3923   |
| 55° | 306    |
| 60° | 263    |
| 65° | 311    |
| 70° | 192    |
| 75° | 254    |
| 80° | 379    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27941 cd/sqm



TEST NUMBER: P1275972  
 CATALOG NUMBER: P3AS09R709835DE010 E3D1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 53.0   | 7.8       |
| 10°-20°   | 143.8  | 21.1      |
| 20°-30°   | 203.5  | 29.9      |
| 30°-40°   | 204.5  | 30.0      |
| 40°-50°   | 73.5   | 10.8      |
| 50°-60°   | 2.0    | 0.3       |
| 60°-70°   | 0.5    | 0.1       |
| 70°-80°   | 0.3    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 400.2  | 58.8      |
| 0°-40°    | 604.7  | 88.8      |
| 0°-60°    | 680.2  | 99.9      |
| 0°-90°    | 681.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 681.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 604 |      |
| 5°  | 567 | 53   |
| 15° | 512 | 144  |
| 25° | 437 | 203  |
| 35° | 341 | 204  |
| 45° | 90  | 74   |
| 55° | 1   | 2    |
| 65° | 1   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1275972  
CATALOG NUMBER: P3AS09R709835DE010 E3D1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 603.9 |
| 1°    | 602.2 |
| 2°    | 596.9 |
| 3°    | 588.5 |
| 4°    | 577.9 |
| 5°    | 567.2 |
| 6°    | 557.2 |
| 7°    | 549.3 |
| 8°    | 542.3 |
| 9°    | 536.7 |
| 10°   | 531.7 |
| 11°   | 527.5 |
| 12°   | 523.6 |
| 13°   | 519.7 |
| 14°   | 516.0 |
| 15°   | 512.1 |
| 16°   | 507.4 |
| 17°   | 502.3 |
| 18°   | 496.2 |
| 19°   | 488.6 |
| 20°   | 480.2 |
| 21°   | 471.0 |
| 22°   | 461.8 |
| 23°   | 452.8 |
| 24°   | 444.2 |
| 25°   | 436.6 |
| 26°   | 431.3 |
| 27°   | 427.1 |
| 28°   | 423.7 |
| 29°   | 419.8 |
| 30°   | 414.2 |
| 31°   | 406.1 |
| 32°   | 394.7 |
| 32.5° | 388.2 |
| 33°   | 379.5 |
| 34°   | 362.5 |
| 35°   | 341.2 |
| 36°   | 317.7 |
| 37°   | 291.2 |
| 37.5° | 278.9 |
| 38°   | 262.1 |
| 39°   | 232.1 |
| 40°   | 206.4 |
| 42.5° | 142.9 |
| 45°   | 90.1  |



TEST NUMBER: P1275972  
CATALOG NUMBER: P3AS09R709835DE010 E3D1WMH

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 47.5° | 48.4 |
| 50°   | 11.5 |
| 52.5° | 1.4  |
| 55°   | 0.8  |
| 57.5° | 0.8  |
| 60°   | 0.6  |
| 62.5° | 0.6  |
| 65°   | 0.6  |
| 67.5° | 0.3  |
| 70°   | 0.3  |
| 72.5° | 0.3  |
| 75°   | 0.3  |
| 77.5° | 0.3  |
| 80°   | 0.3  |
| 82.5° | 0.0  |
| 85°   | 0.0  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)