

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276010

Luminaire Tested: P3AS13R159835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 229.0 lumens
Efficiency: N/A
Efficacy: 15.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276010
CATALOG NUMBER: P3AS13R159835DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1276010
 CATALOG NUMBER: P3AS13R159835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98742
5°	91261
10°	72855
15°	55051
20°	41910
25°	31937
30°	22890
35°	14937
40°	9160
45°	5520
50°	3684
55°	2829
60°	2456
65°	2127
70°	1923
75°	1864
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5520 cd/sqm



TEST NUMBER: P1276010
 CATALOG NUMBER: P3AS13R159835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	16.0
10°-20°	67.8	29.6
20°-30°	60.3	26.3
30°-40°	35.7	15.6
40°-50°	14.6	6.4
50°-60°	6.9	3.0
60°-70°	4.2	1.8
70°-80°	2.2	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.8	72.0
0°-40°	200.5	87.6
0°-60°	222.0	97.0
0°-90°	229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	229.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	450	
5°	415	37
15°	242	68
25°	132	60
35°	56	36
45°	18	15
55°	7	7
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1276010
CATALOG NUMBER: P3AS13R159835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	450.3
1°	449.2
2°	445.9
3°	439.2
4°	428.0
5°	414.6
6°	400.1
7°	383.0
8°	365.2
9°	347.0
10°	327.2
12.5°	282.2
15°	242.5
17.5°	208.2
20°	179.6
22.5°	154.3
25°	132.0
27.5°	110.4
30°	90.4
32.5°	72.1
35°	55.8
37.5°	42.8
40°	32.0
42.5°	23.8
45°	17.8
47.5°	13.8
50°	10.8
52.5°	8.9
55°	7.4
57.5°	6.3
60°	5.6
62.5°	4.8
65°	4.1
67.5°	3.7
70°	3.0
72.5°	2.6
75°	2.2
77.5°	1.5
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)