

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275023

Luminaire Tested: P3AS02R259835DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259835DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 195.0 lumens
Efficiency: N/A
Efficacy: 54.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275023

CATALOG NUMBER: P3AS02R259835DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1275023

CATALOG NUMBER: P3AS02R259835DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	89	88
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	85	84
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	81	80
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	77	76
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	74	73
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	71	70
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	65	64
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125078
5°	116707
10°	93496
15°	63451
20°	38410
25°	22453
30°	12787
35°	7040
40°	3721
45°	1954
50°	1160
55°	841
60°	746
65°	778
70°	705
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1954 cd/sqm

TEST NUMBER: P1275023

CATALOG NUMBER: P3AS02R259835DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	24.1
10°-20°	76.8	39.4
20°-30°	43.9	22.5
30°-40°	17.3	8.9
40°-50°	5.3	2.7
50°-60°	2.1	1.1
60°-70°	1.4	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.8	86.1
0°-40°	185.1	94.9
0°-60°	192.5	98.7
0°-90°	195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	570	
5°	530	47
15°	280	77
25°	93	44
35°	26	17
45°	6	5
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275023

CATALOG NUMBER: P3AS02R259835DE010 E3DL1LI


CANDELA DISTRIBUTION (FULL):

0°	
0°	570.4
1°	569.3
2°	564.7
3°	556.5
4°	545.1
5°	530.2
6°	512.7
7°	492.9
8°	470.0
9°	446.5
10°	419.9
11°	393.6
12°	364.7
13°	336.2
14°	306.9
15°	279.5
17.5°	216.7
20°	164.6
22.5°	123.6
25°	92.8
27.5°	68.8
30°	50.5
32.5°	36.5
35°	26.3
37.5°	18.6
40°	13.0
42.5°	8.9
45°	6.3
47.5°	4.5
50°	3.4
52.5°	2.6
55°	2.2
57.5°	2.0
60°	1.7
62.5°	1.5
65°	1.5
67.5°	1.3
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1275023
CATALOG NUMBER: P3AS02R259835DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):



(END OF REPORT)