

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276043

Luminaire Tested: P3AS13R209835DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209835DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 521.0 lumens
Efficiency: N/A
Efficacy: 35.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276043

CATALOG NUMBER: P3AS13R209835DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1276043

CATALOG NUMBER: P3AS13R209835DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87
3	98	90	83	78	95	88	82	78	85	81	77		83	79	75		80
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		66	61	57		65
7	76	66	59	54	75	65	58	53	63	58	53		62	57	53		61
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147751
5°	137266
10°	116230
15°	90988
20°	71616
25°	57076
30°	45906
35°	37423
40°	30944
45°	26080
50°	22345
55°	19192
60°	16753
65°	14736
70°	12630
75°	11099
80°	8334
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26080 cd/sqm

TEST NUMBER: P1276043

CATALOG NUMBER: P3AS13R209835DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	10.8
10°-20°	112.2	21.5
20°-30°	109.0	20.9
30°-40°	88.0	16.9
40°-50°	65.4	12.6
50°-60°	45.4	8.7
60°-70°	28.5	5.5
70°-80°	13.8	2.7
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.5	53.3
0°-40°	365.5	70.1
0°-60°	476.3	91.4
0°-90°	521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	521.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	674	
5°	624	56
15°	401	112
25°	236	109
35°	140	88
45°	84	65
55°	50	45
65°	28	28
75°	13	14
85°	2	2
90°	0	

TEST NUMBER: P1276043

CATALOG NUMBER: P3AS13R209835DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	673.8
2.5°	658.5
5°	623.6
7.5°	576.6
10°	522.0
12.5°	462.0
15°	400.8
17.5°	350.6
20°	306.9
22.5°	268.7
25°	235.9
27.5°	207.5
30°	181.3
32.5°	159.4
35°	139.8
37.5°	122.3
40°	108.1
42.5°	95.0
45°	84.1
47.5°	74.3
50°	65.5
52.5°	57.9
55°	50.2
57.5°	43.7
60°	38.2
62.5°	33.9
65°	28.4
67.5°	24.0
70°	19.7
72.5°	16.4
75°	13.1
77.5°	9.8
80°	6.6
82.5°	3.3
85°	2.2
87.5°	0.0
90°	0.0

(END OF REPORT)