

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276069

Luminaire Tested: P3AS13R259835DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259835DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 486.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276069

CATALOG NUMBER: P3AS13R259835DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1276069

CATALOG NUMBER: P3AS13R259835DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176455
5°	169271
10°	148294
15°	119206
20°	91591
25°	69294
30°	50084
35°	33274
40°	20181
45°	11753
50°	7505
55°	6079
60°	5307
65°	4722
70°	3911
75°	3813
80°	2904
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11753 cd/sqm

TEST NUMBER: P1276069

CATALOG NUMBER: P3AS13R259835DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	14.4
10°-20°	145.2	29.9
20°-30°	131.3	27.0
30°-40°	78.9	16.2
40°-50°	31.3	6.4
50°-60°	14.4	3.0
60°-70°	8.8	1.8
70°-80°	4.7	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.5	71.3
0°-40°	425.4	87.5
0°-60°	471.2	96.9
0°-90°	486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	486.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	805	
5°	769	70
15°	525	145
25°	286	131
35°	124	79
45°	38	31
55°	16	14
65°	9	9
75°	4	5
85°	2	1
90°	0	

TEST NUMBER: P1276069

CATALOG NUMBER: P3AS13R259835DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	804.7
1°	804.7
2°	800.9
3°	792.5
4°	781.9
5°	769.0
6°	752.4
7°	733.4
8°	711.5
9°	689.5
10°	666.0
11°	638.7
12°	610.7
13°	582.7
14°	554.6
15°	525.1
17.5°	455.4
20°	392.5
22.5°	335.7
25°	286.4
27.5°	240.2
30°	197.8
32.5°	159.1
35°	124.3
37.5°	94.7
40°	70.5
42.5°	51.5
45°	37.9
47.5°	28.8
50°	22.0
52.5°	18.2
55°	15.9
57.5°	13.6
60°	12.1
62.5°	9.8
65°	9.1
67.5°	7.6
70°	6.1
72.5°	5.3
75°	4.5
77.5°	3.8
80°	2.3
82.5°	1.5
85°	1.5
87.5°	0.8



TEST NUMBER: P1276069

CATALOG NUMBER: P3AS13R259835DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)