

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275076

Luminaire Tested: P3AS02R359835DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1275076  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359835DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 237.0 lumens  
Efficiency: N/A  
Efficacy: 65.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275076  
CATALOG NUMBER: P3AS02R359835DE010 E3CB1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1275076

CATALOG NUMBER: P3AS02R359835DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98		96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94		93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90		89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87		86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84		83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81		80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79		77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76		75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74		73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71		70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	154549
5°	151397
10°	140835
15°	103247
20°	52878
25°	19066
30°	7419
35°	2597
40°	1059
45°	279
50°	239
55°	268
60°	263
65°	208
70°	256
75°	339
80°	253
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 339 cd/sqm



TEST NUMBER: P1275076  
 CATALOG NUMBER: P3AS02R359835DE010 E3CB1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.1	27.0
10°-20°	120.3	50.8
20°-30°	42.6	18.0
30°-40°	7.5	3.1
40°-50°	1.1	0.5
50°-60°	0.6	0.3
60°-70°	0.5	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.0	95.8
0°-40°	234.5	98.9
0°-60°	236.1	99.6
0°-90°	237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	237.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	705	
5°	688	64
15°	455	120
25°	79	43
35°	10	7
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1275076  
CATALOG NUMBER: P3AS02R359835DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	704.8
1°	704.6
2°	702.3
3°	698.0
4°	694.1
5°	687.8
6°	681.2
7°	674.0
8°	665.0
9°	651.0
10°	632.5
11°	607.0
12°	576.2
13°	539.6
14°	499.3
15°	454.8
17.5°	338.8
20°	226.6
22.5°	136.6
25°	78.8
27.5°	47.0
30°	29.3
32.5°	17.0
35°	9.7
37.5°	6.2
40°	3.7
42.5°	1.9
45°	0.9
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.7
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1275076  
CATALOG NUMBER: P3AS02R359835DE010 E3CB1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)