

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276135

Luminaire Tested: P3AS13R359835DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359835DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 587.0 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276135
CATALOG NUMBER: P3AS13R359835DE010 E3PHLD1MW

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1276135
 CATALOG NUMBER: P3AS13R359835DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	81	84	81	79	84	81	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	77	73	70	68
4	88	78	71	65	86	77	70	64	75	68	64	72	67	63	70	66	62	70	66	62	60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	65	60	56	54
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	55	50	46	55	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	52	46	42	41
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	48	43	39	38
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	96352	96352	96352
5°	94541	94387	94541
10°	88887	88731	88887
15°	80477	80477	80659
20°	71243	71243	71243
25°	61963	61770	61770
30°	53704	53325	53527
35°	46230	46043	46230
40°	40132	39903	40132
45°	35228	35011	35011
50°	31283	31010	31010
55°	27526	27526	27526
60°	24910	24603	24910
65°	22415	22415	22415
70°	19939	19939	19939
75°	17961	17368	17961
80°	15280	15280	15280
85°	9561	9561	9561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35228 cd/sqm



TEST NUMBER: P1276135
 CATALOG NUMBER: P3AS13R359835DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	6.8
10°-20°	98.9	16.8
20°-30°	117.5	20.0
30°-40°	108.0	18.4
40°-50°	87.7	14.9
50°-60°	64.9	11.1
60°-70°	42.9	7.3
70°-80°	22.2	3.8
80°-90°	5.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.4	43.7
0°-40°	364.4	62.1
0°-60°	516.9	88.1
0°-90°	587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	439	439	439	439	439	
5°	430	429	429	429	430	40
15°	354	354	354	354	355	99
25°	256	255	255	256	255	118
35°	173	172	172	173	173	108
45°	114	113	113	113	113	88
55°	72	72	72	72	72	65
65°	43	43	43	43	43	43
75°	21	21	20	21	21	22
85°	4	4	4	4	4	5
90°	0	0	0	0	0	



TEST NUMBER: P1276135

CATALOG NUMBER: P3AS13R359835DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	439.4	439.4	439.4	439.4	439.4
1°	439.4	438.6	438.6	438.6	439.4
2°	437.9	437.9	437.9	437.9	437.9
3°	436.4	435.6	435.6	435.6	435.6
4°	433.3	432.6	432.6	432.6	432.6
5°	429.5	428.8	428.8	428.8	429.5
6°	425.0	424.2	423.5	423.5	424.2
7°	420.5	418.9	418.9	418.9	418.9
8°	413.6	412.9	412.9	412.9	412.9
9°	406.8	405.3	406.1	406.1	406.1
10°	399.2	398.5	398.5	398.5	399.2
11°	391.7	390.9	390.9	390.1	390.9
12°	382.6	382.6	382.6	382.6	382.6
13°	374.2	373.5	373.5	373.5	374.2
14°	365.1	364.4	364.4	364.4	364.4
15°	354.5	354.5	354.5	354.5	355.3
17.5°	330.3	329.5	330.3	330.3	331.1
20°	305.3	304.5	305.3	305.3	305.3
22.5°	280.3	280.3	279.5	280.3	281.1
25°	256.1	255.3	255.3	256.1	255.3
27.5°	233.3	232.6	232.6	232.6	232.6
30°	212.1	210.6	210.6	211.4	211.4
32.5°	190.2	190.2	190.9	190.2	190.2
35°	172.7	172.0	172.0	172.7	172.7
37.5°	155.3	154.5	154.5	155.3	155.3
40°	140.2	140.2	139.4	140.2	140.2
42.5°	125.8	125.8	125.8	125.8	125.8
45°	113.6	112.9	112.9	112.9	112.9
47.5°	101.5	101.5	101.5	100.8	101.5
50°	91.7	90.9	90.9	90.9	90.9
52.5°	81.1	81.1	81.1	81.1	81.1
55°	72.0	72.0	72.0	72.0	72.0
57.5°	64.4	63.6	63.6	63.6	63.6
60°	56.8	56.8	56.1	56.8	56.8
62.5°	49.2	49.2	49.2	49.2	49.2
65°	43.2	43.2	43.2	43.2	43.2
67.5°	37.1	37.1	37.1	37.1	37.1
70°	31.1	31.1	31.1	31.1	31.1
72.5°	26.5	25.8	25.8	25.8	25.8
75°	21.2	21.2	20.5	21.2	21.2
77.5°	15.9	15.9	15.9	15.9	15.9
80°	12.1	12.1	12.1	11.4	12.1
82.5°	7.6	7.6	7.6	7.6	7.6
85°	3.8	3.8	3.8	3.8	3.8
87.5°	0.8	0.8	0.8	1.5	1.5



TEST NUMBER: P1276135
CATALOG NUMBER: P3AS13R359835DE010 E3PHLD1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)