

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275117

Luminaire Tested: P3AS02R409835DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275117
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409835DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 137.0 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275117
CATALOG NUMBER: P3AS02R409835DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1275117
 CATALOG NUMBER: P3AS02R409835DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	95	95	95	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	88	88	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	81	81	81	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	76	76	76	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	71	71	71	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	66	66	66	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	62	62	62	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	59	59	59	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	56	56	56	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	53	53	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42650
5°	41800
10°	38922
15°	33916
20°	27326
25°	20493
30°	14407
35°	9450
40°	5725
45°	3411
50°	2047
55°	1644
60°	1491
65°	1245
70°	1218
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3411 cd/sqm



TEST NUMBER: P1275117
 CATALOG NUMBER: P3AS02R409835DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.6	12.9
10°-20°	41.1	30.0
20°-30°	38.8	28.3
30°-40°	22.4	16.4
40°-50°	8.9	6.5
50°-60°	4.0	2.9
60°-70°	2.5	1.8
70°-80°	1.3	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	97.5	71.2
0°-40°	120.0	87.6
0°-60°	132.9	97.0
0°-90°	137.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	137.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	194	
5°	190	18
15°	149	41
25°	85	39
35°	35	22
45°	11	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275117

CATALOG NUMBER: P3AS02R409835DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	194.5
2.5°	193.4
5°	189.9
7.5°	183.3
10°	174.8
12.5°	163.2
15°	149.4
17.5°	133.9
20°	117.1
22.5°	100.3
25°	84.7
27.5°	70.1
30°	56.9
32.5°	45.3
35°	35.3
37.5°	26.7
40°	20.0
42.5°	14.9
45°	11.0
47.5°	8.0
50°	6.0
52.5°	4.8
55°	4.3
57.5°	3.9
60°	3.4
62.5°	2.8
65°	2.4
67.5°	2.1
70°	1.9
72.5°	1.5
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)