

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276154

Luminaire Tested: P3AS13R409835DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409835DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 332.0 lumens
Efficiency: N/A
Efficacy: 22.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276154
CATALOG NUMBER: P3AS13R409835DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1276154
 CATALOG NUMBER: P3AS13R409835DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74534
5°	73167
10°	68981
15°	62656
20°	55048
25°	47011
30°	38943
35°	30035
40°	21383
45°	14389
50°	7846
55°	5543
60°	5219
65°	4825
70°	4296
75°	4067
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14389 cd/sqm



TEST NUMBER: P1276154
 CATALOG NUMBER: P3AS13R409835DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.0	9.3
10°-20°	76.9	23.2
20°-30°	88.9	26.8
30°-40°	70.0	21.1
40°-50°	35.9	10.8
50°-60°	13.7	4.1
60°-70°	9.1	2.7
70°-80°	4.9	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.8	59.3
0°-40°	266.8	80.4
0°-60°	316.5	95.3
0°-90°	332.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	332.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	340	
5°	332	31
15°	276	77
25°	194	89
35°	112	70
45°	46	36
55°	14	14
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1276154
CATALOG NUMBER: P3AS13R409835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	339.9
2.5°	338.0
5°	332.4
7.5°	322.8
10°	309.8
12.5°	294.6
15°	276.0
17.5°	256.7
20°	235.9
22.5°	214.7
25°	194.3
27.5°	173.8
30°	153.8
32.5°	133.3
35°	112.2
37.5°	92.5
40°	74.7
42.5°	59.4
45°	46.4
47.5°	33.8
50°	23.0
52.5°	16.7
55°	14.5
57.5°	13.0
60°	11.9
62.5°	10.4
65°	9.3
67.5°	7.8
70°	6.7
72.5°	5.6
75°	4.8
77.5°	3.7
80°	2.6
82.5°	2.2
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)