

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275125

Luminaire Tested: P3AS02R409835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 67.0 lumens
Efficiency: N/A
Efficacy: 18.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275125

CATALOG NUMBER: P3AS02R409835DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1275125

CATALOG NUMBER: P3AS02R409835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20854
5°	20449
10°	19038
15°	16595
20°	13371
25°	10017
30°	7039
35°	4604
40°	2805
45°	1675
50°	989
55°	803
60°	702
65°	623
70°	577
75°	424
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1675 cd/sqm

TEST NUMBER: P1275125

CATALOG NUMBER: P3AS02R409835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.6	12.9
10°-20°	20.1	30.0
20°-30°	19.0	28.3
30°-40°	11.0	16.4
40°-50°	4.4	6.5
50°-60°	1.9	2.9
60°-70°	1.2	1.8
70°-80°	0.6	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	47.7	71.2
0°-40°	58.7	87.6
0°-60°	65.0	97.0
0°-90°	67.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	67.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	95	
5°	93	9
15°	73	20
25°	41	19
35°	17	11
45°	5	4
55°	2	2
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1275125

CATALOG NUMBER: P3AS02R409835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	95.1
2.5°	94.6
5°	92.9
7.5°	89.7
10°	85.5
12.5°	79.8
15°	73.1
17.5°	65.5
20°	57.3
22.5°	49.1
25°	41.4
27.5°	34.3
30°	27.8
32.5°	22.2
35°	17.2
37.5°	13.0
40°	9.8
42.5°	7.3
45°	5.4
47.5°	3.9
50°	2.9
52.5°	2.4
55°	2.1
57.5°	1.9
60°	1.6
62.5°	1.4
65°	1.2
67.5°	1.0
70°	0.9
72.5°	0.7
75°	0.5
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)