

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276219

Luminaire Tested: P3AS13R509835DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509835DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 559.0 lumens
Efficiency: N/A
Efficacy: 38.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276219

CATALOG NUMBER: P3AS13R509835DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1276219

CATALOG NUMBER: P3AS13R509835DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		73
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		53
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162575
5°	158199
10°	145889
15°	128309
20°	107343
25°	85118
30°	62440
35°	42938
40°	27280
45°	15257
50°	8256
55°	6958
60°	5964
65°	5500
70°	4873
75°	4490
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 15257 cd/sqm

TEST NUMBER: P1276219

CATALOG NUMBER: P3AS13R509835DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.6	11.9
10°-20°	156.5	28.0
20°-30°	160.1	28.6
30°-40°	101.5	18.2
40°-50°	40.4	7.2
50°-60°	16.4	2.9
60°-70°	10.5	1.9
70°-80°	5.4	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.2	68.5
0°-40°	484.7	86.7
0°-60°	541.5	96.9
0°-90°	559.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	559.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	741	
5°	719	67
15°	565	157
25°	352	160
35°	160	102
45°	49	40
55°	18	16
65°	11	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1276219

CATALOG NUMBER: P3AS13R509835DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	741.4
2.5°	736.1
5°	718.7
7.5°	691.5
10°	655.2
12.5°	612.1
15°	565.2
17.5°	513.7
20°	460.0
22.5°	406.3
25°	351.8
27.5°	297.3
30°	246.6
32.5°	201.2
35°	160.4
37.5°	125.6
40°	95.3
42.5°	70.4
45°	49.2
47.5°	33.3
50°	24.2
52.5°	20.4
55°	18.2
57.5°	15.9
60°	13.6
62.5°	12.1
65°	10.6
67.5°	9.1
70°	7.6
72.5°	6.1
75°	5.3
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)