

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275148

Luminaire Tested: P3AS02R459835DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1275148  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R459835DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 162.0 lumens  
Efficiency: N/A  
Efficacy: 45.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275148  
CATALOG NUMBER: P3AS02R459835DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1275148

CATALOG NUMBER: P3AS02R459835DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34339
5°	33744
10°	31930
15°	29126
20°	25739
25°	22356
30°	19193
35°	15981
40°	11908
45°	7288
50°	3377
55°	2638
60°	2544
65°	2335
70°	2180
75°	2033
80°	1894
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7288 cd/sqm



TEST NUMBER: P1275148  
 CATALOG NUMBER: P3AS02R459835DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	14.3	8.8
10°-20°	35.7	22.0
20°-30°	42.4	26.2
30°-40°	36.9	22.8
40°-50°	18.5	11.4
50°-60°	6.4	4.0
60°-70°	4.5	2.8
70°-80°	2.5	1.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	92.5	57.1
0°-40°	129.3	79.8
0°-60°	154.2	95.2
0°-90°	162.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	162.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	157	
5°	153	14
15°	128	36
25°	92	42
35°	60	37
45°	24	18
55°	7	6
65°	4	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1275148  
CATALOG NUMBER: P3AS02R459835DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	156.6
2.5°	155.9
5°	153.3
7.5°	149.2
10°	143.4
12.5°	136.3
15°	128.3
17.5°	119.3
20°	110.3
22.5°	101.2
25°	92.4
27.5°	84.0
30°	75.8
32.5°	68.0
35°	59.7
37.5°	51.0
40°	41.6
42.5°	32.5
45°	23.5
47.5°	15.5
50°	9.9
52.5°	7.7
55°	6.9
57.5°	6.3
60°	5.8
62.5°	5.2
65°	4.5
67.5°	3.9
70°	3.4
72.5°	2.8
75°	2.4
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)