

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276259

Luminaire Tested: P3AS13R609835DE010 E3D1WMH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276259  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R609835DE010 E3D1WMH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 907.0 lumens  
Efficiency: N/A  
Efficacy: 62.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276259  
CATALOG NUMBER: P3AS13R609835DE010 E3D1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1276259

CATALOG NUMBER: P3AS13R609835DE010 E3D1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	237656
5°	224345
10°	218522
15°	213509
20°	198537
25°	177470
30°	135565
35°	78273
40°	30371
45°	12652
50°	2797
55°	421
60°	307
65°	208
70°	256
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12652 cd/sqm



TEST NUMBER: P1276259  
 CATALOG NUMBER: P3AS13R609835DE010 E3D1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.2	10.6
10°-20°	262.0	28.9
20°-30°	328.1	36.2
30°-40°	183.4	20.2
40°-50°	34.9	3.8
50°-60°	1.8	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.4	75.7
0°-40°	869.8	95.9
0°-60°	906.4	99.9
0°-90°	907.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	907.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1084	
5°	1019	96
15°	940	262
25°	734	328
35°	292	183
45°	41	35
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1276259  
CATALOG NUMBER: P3AS13R609835DE010 E3D1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1083.8
1°	1079.3
2°	1065.2
3°	1048.5
4°	1032.9
5°	1019.2
6°	1008.8
7°	999.9
8°	993.2
9°	986.9
10°	981.4
11°	975.8
12°	969.5
13°	961.7
14°	952.4
15°	940.5
16°	926.1
17°	909.7
18°	891.2
19°	870.0
20°	850.8
21°	830.0
22°	808.5
23°	785.8
24°	761.0
25°	733.5
26°	701.2
27°	665.2
28°	624.8
29°	581.8
30°	535.4
31°	488.6
32°	440.4
32.5°	414.1
33°	390.3
34°	341.0
35°	292.4
36°	248.6
37°	202.2
37.5°	181.1
38°	160.3
39°	129.1
40°	106.1
42.5°	64.6
45°	40.8



TEST NUMBER: P1276259  
CATALOG NUMBER: P3AS13R609835DE010 E3D1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	22.6
50°	8.2
52.5°	1.9
55°	1.1
57.5°	0.7
60°	0.7
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)