

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276295

Luminaire Tested: P3AS13R659835DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659835DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 292.0 lumens
Efficiency: N/A
Efficacy: 20.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276295

CATALOG NUMBER: P3AS13R659835DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276295

CATALOG NUMBER: P3AS13R659835DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51970
5°	51266
10°	49543
15°	46720
20°	43100
25°	39123
30°	34638
35°	29473
40°	23473
45°	16560
50°	9620
55°	5238
60°	4868
65°	4410
70°	4039
75°	3813
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16560 cd/sqm

TEST NUMBER: P1276295

CATALOG NUMBER: P3AS13R659835DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.9	7.5
10°-20°	57.6	19.7
20°-30°	74.0	25.3
30°-40°	68.4	23.4
40°-50°	41.3	14.2
50°-60°	14.1	4.8
60°-70°	8.5	2.9
70°-80°	4.8	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	153.5	52.6
0°-40°	221.9	76.0
0°-60°	277.3	95.0
0°-90°	292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	292.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	237	
5°	233	22
15°	206	58
25°	162	74
35°	110	68
45°	53	41
55°	14	14
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1276295

CATALOG NUMBER: P3AS13R659835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	237.0
2.5°	235.9
5°	232.9
7.5°	228.4
10°	222.5
12.5°	215.1
15°	205.8
17.5°	195.8
20°	184.7
22.5°	173.2
25°	161.7
27.5°	149.4
30°	136.8
32.5°	124.2
35°	110.1
37.5°	96.4
40°	82.0
42.5°	67.5
45°	53.4
47.5°	40.4
50°	28.2
52.5°	17.8
55°	13.7
57.5°	12.2
60°	11.1
62.5°	9.6
65°	8.5
67.5°	7.4
70°	6.3
72.5°	5.6
75°	4.5
77.5°	3.7
80°	2.6
82.5°	1.9
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)