

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275217

Luminaire Tested: P3AS02R609835DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609835DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 241.0 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275217

CATALOG NUMBER: P3AS02R609835DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1275217

CATALOG NUMBER: P3AS02R609835DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	78	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		78	70	64	60		69	64	60		68	63	60		67	62	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57539
5°	55272
10°	56891
15°	57639
20°	50894
25°	42898
30°	34790
35°	22647
40°	10391
45°	4000
50°	1330
55°	344
60°	307
65°	311
70°	256
75°	339
80°	253
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4000 cd/sqm

TEST NUMBER: P1275217

CATALOG NUMBER: P3AS02R609835DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.2	10.0
10°-20°	69.5	28.8
20°-30°	81.1	33.6
30°-40°	52.3	21.7
40°-50°	11.7	4.9
50°-60°	1.1	0.5
60°-70°	0.6	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	174.8	72.5
0°-40°	227.1	94.2
0°-60°	240.0	99.6
0°-90°	241.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	241.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	262	
5°	251	24
15°	254	70
25°	177	81
35°	85	52
45°	13	12
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1275217

CATALOG NUMBER: P3AS02R609835DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	262.4
2.5°	258.2
5°	251.1
7.5°	250.7
10°	255.5
12.5°	258.7
15°	253.9
17.5°	239.3
20°	218.1
22.5°	195.9
25°	177.3
27.5°	159.0
30°	137.4
32.5°	112.0
35°	84.6
37.5°	57.8
40°	36.3
42.5°	21.8
45°	12.9
47.5°	7.5
50°	3.9
52.5°	1.3
55°	0.9
57.5°	0.7
60°	0.7
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)