

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276349

Luminaire Tested: P3AS17R159835DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159835DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 473.9 lumens
Efficiency: N/A
Efficacy: 23.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276349

CATALOG NUMBER: P3AS17R159835DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276349

CATALOG NUMBER: P3AS17R159835DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119552
5°	116311
10°	106300
15°	93099
20°	79877
25°	66681
30°	53375
35°	40020
40°	29054
45°	18979
50°	11872
55°	8028
60°	7105
65°	6538
70°	6155
75°	5592
80°	5304
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18979 cd/sqm

TEST NUMBER: P1276349

CATALOG NUMBER: P3AS17R159835DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	10.3
10°-20°	114.3	24.1
20°-30°	125.9	26.6
30°-40°	94.3	19.9
40°-50°	48.9	10.3
50°-60°	20.2	4.3
60°-70°	12.5	2.6
70°-80°	7.0	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.9	61.0
0°-40°	383.2	80.9
0°-60°	452.3	95.4
0°-90°	473.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	473.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	545	
5°	528	49
15°	410	114
25°	276	126
35°	150	94
45°	61	49
55°	21	20
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1276349

CATALOG NUMBER: P3AS17R159835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	545.2
1°	545.8
2°	544.0
3°	540.4
4°	535.0
5°	528.4
6°	520.0
7°	511.0
8°	500.2
9°	488.8
10°	477.4
12.5°	444.4
15°	410.1
17.5°	375.9
20°	342.3
22.5°	308.0
25°	275.6
27.5°	243.2
30°	210.8
32.5°	178.9
35°	149.5
37.5°	124.3
40°	101.5
42.5°	80.5
45°	61.2
47.5°	46.2
50°	34.8
52.5°	25.8
55°	21.0
57.5°	18.6
60°	16.2
62.5°	14.4
65°	12.6
67.5°	10.8
70°	9.6
72.5°	7.8
75°	6.6
77.5°	5.4
80°	4.2
82.5°	3.0
85°	1.8
87.5°	0.6
90°	0.0

(END OF REPORT)