

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276357

Luminaire Tested: P3AS17R159835DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159835DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 755.0 lumens
Efficiency: N/A
Efficacy: 37.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276357

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1276357

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325566
5°	300902
10°	240232
15°	181477
20°	138192
25°	105296
30°	75429
35°	49229
40°	30171
45°	18234
50°	12145
55°	9366
60°	8070
65°	7005
70°	6283
75°	6270
80°	4672
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18234 cd/sqm

TEST NUMBER: P1276357

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.1	16.0
10°-20°	223.4	29.6
20°-30°	198.9	26.3
30°-40°	117.7	15.6
40°-50°	48.3	6.4
50°-60°	22.7	3.0
60°-70°	13.8	1.8
70°-80°	7.3	1.0
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.4	72.0
0°-40°	661.1	87.6
0°-60°	732.1	97.0
0°-90°	755.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	755.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1485	
5°	1367	121
15°	799	223
25°	435	199
35°	184	118
45°	59	48
55°	24	23
65°	14	14
75°	7	7
85°	1	2
90°	0	

TEST NUMBER: P1276357

CATALOG NUMBER: P3AS17R159835DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1484.7
1°	1481.1
2°	1470.0
3°	1447.9
4°	1411.2
5°	1367.0
6°	1319.2
7°	1262.8
8°	1204.0
9°	1143.9
10°	1078.9
12.5°	930.6
15°	799.4
17.5°	686.6
20°	592.2
22.5°	508.8
25°	435.2
27.5°	364.1
30°	297.9
32.5°	237.9
35°	183.9
37.5°	141.0
40°	105.4
42.5°	78.5
45°	58.8
47.5°	45.4
50°	35.6
52.5°	29.4
55°	24.5
57.5°	20.8
60°	18.4
62.5°	15.9
65°	13.5
67.5°	12.3
70°	9.8
72.5°	8.6
75°	7.4
77.5°	4.9
80°	3.7
82.5°	2.5
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)