

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275281

Luminaire Tested: P3AS02R709835DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1275281  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R709835DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 223.0 lumens  
Efficiency: N/A  
Efficacy: 62.0 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275281

CATALOG NUMBER: P3AS02R709835DE010 E3D1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1275281

CATALOG NUMBER: P3AS02R709835DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  |  | 88  | 84  | 81  |  | 86  |
| 4   | 95  | 87  | 81  | 77  | 94  | 86  | 81  | 76  | 84  | 79  | 76  |  | 82  | 78  | 75  |  | 80  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  |
| 6   | 85  | 75  | 69  | 64  | 83  | 75  | 69  | 64  | 73  | 68  | 64  |  | 72  | 67  | 63  |  | 70  |
| 7   | 80  | 70  | 64  | 59  | 79  | 70  | 63  | 59  | 68  | 63  | 59  |  | 67  | 62  | 58  |  | 66  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  |  | 63  | 58  | 54  |  | 62  |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  |  | 55  | 50  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 43352 |
| 5°  | 40876 |
| 10° | 38766 |
| 15° | 38071 |
| 20° | 36707 |
| 25° | 34599 |
| 30° | 34334 |
| 35° | 29901 |
| 40° | 19351 |
| 45° | 9148  |
| 50° | 1296  |
| 55° | 115   |
| 60° | 88    |
| 65° | 104   |
| 70° | 64    |
| 75° | 85    |
| 80° | 126   |
| 85° | 0     |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9148 cd/sqm

TEST NUMBER: P1275281

CATALOG NUMBER: P3AS02R709835DE010 E3D1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 17.3   | 7.8       |
| 10°-20°   | 47.1   | 21.1      |
| 20°-30°   | 66.6   | 29.9      |
| 30°-40°   | 66.9   | 30.0      |
| 40°-50°   | 24.1   | 10.8      |
| 50°-60°   | 0.7    | 0.3       |
| 60°-70°   | 0.2    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 131.1  | 58.8      |
| 0°-40°    | 198.0  | 88.8      |
| 0°-60°    | 222.8  | 99.9      |
| 0°-90°    | 223.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 223.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 198 |      |
| 5°  | 186 | 17   |
| 15° | 168 | 47   |
| 25° | 143 | 67   |
| 35° | 112 | 67   |
| 45° | 30  | 24   |
| 55° | 0   | 1    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1275281

CATALOG NUMBER: P3AS02R709835DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 197.7 |
| 1°    | 197.2 |
| 2°    | 195.5 |
| 3°    | 192.7 |
| 4°    | 189.2 |
| 5°    | 185.7 |
| 6°    | 182.4 |
| 7°    | 179.9 |
| 8°    | 177.6 |
| 9°    | 175.8 |
| 10°   | 174.1 |
| 11°   | 172.7 |
| 12°   | 171.5 |
| 13°   | 170.2 |
| 14°   | 169.0 |
| 15°   | 167.7 |
| 16°   | 166.1 |
| 17°   | 164.5 |
| 18°   | 162.5 |
| 19°   | 160.0 |
| 20°   | 157.3 |
| 21°   | 154.2 |
| 22°   | 151.2 |
| 23°   | 148.3 |
| 24°   | 145.4 |
| 25°   | 143.0 |
| 26°   | 141.2 |
| 27°   | 139.9 |
| 28°   | 138.8 |
| 29°   | 137.5 |
| 30°   | 135.6 |
| 31°   | 133.0 |
| 32°   | 129.2 |
| 32.5° | 127.1 |
| 33°   | 124.3 |
| 34°   | 118.7 |
| 35°   | 111.7 |
| 36°   | 104.0 |
| 37°   | 95.3  |
| 37.5° | 91.3  |
| 38°   | 85.8  |
| 39°   | 76.0  |
| 40°   | 67.6  |
| 42.5° | 46.8  |
| 45°   | 29.5  |

TEST NUMBER: P1275281

CATALOG NUMBER: P3AS02R709835DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 47.5° | 15.8 |
| 50°   | 3.8  |
| 52.5° | 0.5  |
| 55°   | 0.3  |
| 57.5° | 0.3  |
| 60°   | 0.2  |
| 62.5° | 0.2  |
| 65°   | 0.2  |
| 67.5° | 0.1  |
| 70°   | 0.1  |
| 72.5° | 0.1  |
| 75°   | 0.1  |
| 77.5° | 0.1  |
| 80°   | 0.1  |
| 82.5° | 0.0  |
| 85°   | 0.0  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)