

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275282

Luminaire Tested: P3AS02R709835DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275282
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709835DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 223.0 lumens
Efficiency: N/A
Efficacy: 62.0 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275282

CATALOG NUMBER: P3AS02R709835DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1275282

CATALOG NUMBER: P3AS02R709835DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	76	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43352
5°	40876
10°	38766
15°	38071
20°	36707
25°	34599
30°	34334
35°	29901
40°	19351
45°	9148
50°	1296
55°	115
60°	88
65°	104
70°	64
75°	85
80°	126
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9148 cd/sqm

TEST NUMBER: P1275282

CATALOG NUMBER: P3AS02R709835DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.3	7.8
10°-20°	47.1	21.1
20°-30°	66.6	29.9
30°-40°	66.9	30.0
40°-50°	24.1	10.8
50°-60°	0.7	0.3
60°-70°	0.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	131.1	58.8
0°-40°	198.0	88.8
0°-60°	222.8	99.9
0°-90°	223.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	223.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	198	
5°	186	17
15°	168	47
25°	143	67
35°	112	67
45°	30	24
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1275282

CATALOG NUMBER: P3AS02R709835DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	197.7
1°	197.2
2°	195.5
3°	192.7
4°	189.2
5°	185.7
6°	182.4
7°	179.9
8°	177.6
9°	175.8
10°	174.1
11°	172.7
12°	171.5
13°	170.2
14°	169.0
15°	167.7
16°	166.1
17°	164.5
18°	162.5
19°	160.0
20°	157.3
21°	154.2
22°	151.2
23°	148.3
24°	145.4
25°	143.0
26°	141.2
27°	139.9
28°	138.8
29°	137.5
30°	135.6
31°	133.0
32°	129.2
32.5°	127.1
33°	124.3
34°	118.7
35°	111.7
36°	104.0
37°	95.3
37.5°	91.3
38°	85.8
39°	76.0
40°	67.6
42.5°	46.8
45°	29.5



TEST NUMBER: P1275282

CATALOG NUMBER: P3AS02R709835DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	15.8
50°	3.8
52.5°	0.5
55°	0.3
57.5°	0.3
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.1
77.5°	0.1
80°	0.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)