

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276389

Luminaire Tested: P3AS17R209835DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209835DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 601.0 lumens
Efficiency: N/A
Efficacy: 29.5 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276389
CATALOG NUMBER: P3AS17R209835DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1276389
 CATALOG NUMBER: P3AS17R209835DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81				81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68				68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63				63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55				55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	213711
5°	199361
10°	165417
15°	126493
20°	94928
25°	71472
30°	52844
35°	36942
40°	25305
45°	17552
50°	15078
55°	14872
60°	15525
65°	15618
70°	15900
75°	16521
80°	17932
85°	17863

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 20832 cd/sqm



TEST NUMBER: P1276389

CATALOG NUMBER: P3AS17R209835DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.1	13.5
10°-20°	154.9	25.8
20°-30°	136.3	22.7
30°-40°	88.0	14.6
40°-50°	46.6	7.8
50°-60°	35.0	5.8
60°-70°	29.8	5.0
70°-80°	21.0	3.5
80°-90°	8.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.4	62.0
0°-40°	460.3	76.6
0°-60°	542.0	90.2
0°-90°	601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	975	
5°	906	81
15°	557	155
25°	295	136
35°	138	88
45°	57	47
55°	39	35
65°	30	30
75°	20	21
85°	7	8
90°	0	



TEST NUMBER: P1276389
CATALOG NUMBER: P3AS17R209835DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	974.6
2.5°	955.2
5°	905.7
7.5°	829.6
10°	742.9
12.5°	647.4
15°	557.2
17.5°	475.8
20°	406.8
22.5°	348.5
25°	295.4
27.5°	249.4
30°	208.7
32.5°	171.6
35°	138.0
37.5°	111.4
40°	88.4
42.5°	70.8
45°	56.6
47.5°	49.5
50°	44.2
52.5°	40.7
55°	38.9
57.5°	37.1
60°	35.4
62.5°	31.8
65°	30.1
67.5°	28.3
70°	24.8
72.5°	23.0
75°	19.5
77.5°	17.7
80°	14.2
82.5°	12.4
85°	7.1
87.5°	3.5
90°	0.0

(END OF REPORT)