

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275320

Luminaire Tested: P3AS05R159835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275320
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 117.0 lumens
Efficiency: N/A
Efficacy: 16.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275320

CATALOG NUMBER: P3AS05R159835DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1275320

CATALOG NUMBER: P3AS05R159835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50456
5°	46621
10°	37229
15°	28127
20°	21422
25°	16307
30°	11698
35°	7629
40°	4666
45°	2822
50°	1876
55°	1453
60°	1228
65°	1090
70°	962
75°	932
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2822 cd/sqm

TEST NUMBER: P1275320

CATALOG NUMBER: P3AS05R159835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.8	16.0
10°-20°	34.6	29.6
20°-30°	30.8	26.3
30°-40°	18.2	15.6
40°-50°	7.5	6.4
50°-60°	3.5	3.0
60°-70°	2.1	1.8
70°-80°	1.1	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	84.2	72.0
0°-40°	102.4	87.6
0°-60°	113.4	97.0
0°-90°	117.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	117.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	230	
5°	212	19
15°	124	35
25°	67	31
35°	28	18
45°	9	7
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275320

CATALOG NUMBER: P3AS05R159835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	230.1
1°	229.5
2°	227.8
3°	224.4
4°	218.7
5°	211.8
6°	204.4
7°	195.7
8°	186.6
9°	177.3
10°	167.2
12.5°	144.2
15°	123.9
17.5°	106.4
20°	91.8
22.5°	78.8
25°	67.4
27.5°	56.4
30°	46.2
32.5°	36.9
35°	28.5
37.5°	21.8
40°	16.3
42.5°	12.2
45°	9.1
47.5°	7.0
50°	5.5
52.5°	4.6
55°	3.8
57.5°	3.2
60°	2.8
62.5°	2.5
65°	2.1
67.5°	1.9
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)