

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276429

Luminaire Tested: P3AS17R309835DE010 E3D1LI

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1276429  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R309835DE010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1548.0 lumens  
Efficiency: N/A  
Efficacy: 75.9 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276429

CATALOG NUMBER: P3AS17R309835DE010 E3D1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1276429

CATALOG NUMBER: P3AS17R309835DE010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 |  | 103 | 102 | 101 |  | 100 |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  |  | 100 | 98  | 97  |  | 97  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 97  | 95  |  | 97  | 95  | 93  |  | 95  |
| 4   | 105 | 99  | 95  | 92  | 103 | 98  | 95  | 92  | 96  | 93  | 91  |  | 94  | 92  | 90  |  | 93  |
| 5   | 101 | 96  | 92  | 89  | 100 | 95  | 91  | 88  | 93  | 90  | 87  |  | 92  | 89  | 87  |  | 90  |
| 6   | 99  | 92  | 88  | 85  | 97  | 92  | 88  | 85  | 90  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 7   | 96  | 89  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  |  | 87  | 84  | 81  |  | 86  |
| 8   | 93  | 87  | 83  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  |  | 84  | 81  | 79  |  | 84  |
| 9   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  |  | 82  | 79  | 77  |  | 82  |
| 10  | 88  | 82  | 78  | 75  | 88  | 81  | 78  | 75  | 81  | 77  | 75  |  | 80  | 77  | 75  |  | 80  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1231634 |
| 5°  | 1215581 |
| 10° | 1061303 |
| 15° | 674578  |
| 20° | 267260  |
| 25° | 89279   |
| 30° | 41525   |
| 35° | 18819   |
| 40° | 7214    |
| 45° | 3535    |
| 50° | 1023    |
| 55° | 459     |
| 60° | 263     |
| 65° | 311     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3535 cd/sqm

TEST NUMBER: P1276429

CATALOG NUMBER: P3AS17R309835DE010 E3D1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 504.9  | 32.6      |
| 10°-20°   | 783.0  | 50.6      |
| 20°-30°   | 201.9  | 13.0      |
| 30°-40°   | 47.4   | 3.1       |
| 40°-50°   | 9.2    | 0.6       |
| 50°-60°   | 1.1    | 0.1       |
| 60°-70°   | 0.5    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1489.7 | 96.2      |
| 0°-40°    | 1537.2 | 99.3      |
| 0°-60°    | 1547.5 | 100.0     |
| 0°-90°    | 1548.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1548.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5617 |      |
| 5°  | 5522 | 505  |
| 15° | 2972 | 783  |
| 25° | 369  | 202  |
| 35° | 70   | 47   |
| 45° | 11   | 9    |
| 55° | 1    | 1    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1276429

CATALOG NUMBER: P3AS17R309835DE010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5616.7 |
| 1°    | 5612.5 |
| 2°    | 5599.3 |
| 3°    | 5584.3 |
| 4°    | 5562.0 |
| 5°    | 5522.4 |
| 6°    | 5458.1 |
| 7°    | 5351.1 |
| 8°    | 5205.1 |
| 9°    | 5014.6 |
| 10°   | 4766.4 |
| 11°   | 4471.4 |
| 12°   | 4149.3 |
| 13°   | 3778.5 |
| 14°   | 3390.3 |
| 15°   | 2971.5 |
| 16°   | 2561.1 |
| 17°   | 2165.7 |
| 18°   | 1786.5 |
| 19°   | 1438.6 |
| 20°   | 1145.3 |
| 21°   | 901.4  |
| 22°   | 709.1  |
| 23°   | 561.3  |
| 24°   | 449.5  |
| 25°   | 369.0  |
| 26°   | 307.7  |
| 27°   | 261.4  |
| 28°   | 225.9  |
| 29°   | 193.5  |
| 30°   | 164.0  |
| 32.5° | 103.4  |
| 35°   | 70.3   |
| 37.5° | 43.9   |
| 40°   | 25.2   |
| 42.5° | 16.8   |
| 45°   | 11.4   |
| 47.5° | 6.6    |
| 50°   | 3.0    |
| 52.5° | 1.2    |
| 55°   | 1.2    |
| 57.5° | 0.6    |
| 60°   | 0.6    |
| 62.5° | 0.6    |
| 65°   | 0.6    |

TEST NUMBER: P1276429

CATALOG NUMBER: P3AS17R309835DE010 E3D1LI

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.6 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)