

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276435

Luminaire Tested: P3AS17R309835DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276435  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R309835DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1299.0 lumens  
Efficiency: N/A  
Efficacy: 63.7 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276435  
CATALOG NUMBER: P3AS17R309835DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1276435  
 CATALOG NUMBER: P3AS17R309835DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	91	89	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	88	85	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	79	75	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	76	72	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	758009
5°	721460
10°	606847
15°	437642
20°	271460
25°	154388
30°	85760
35°	46659
40°	24589
45°	13304
50°	7130
55°	4702
60°	4298
65°	4462
70°	3911
75°	3135
80°	3157
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13304 cd/sqm



TEST NUMBER: P1276435  
 CATALOG NUMBER: P3AS17R309835DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	295.1	22.7
10°-20°	524.6	40.4
20°-30°	303.2	23.3
30°-40°	115.1	8.9
40°-50°	35.3	2.7
50°-60°	11.9	0.9
60°-70°	8.1	0.6
70°-80°	4.4	0.3
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1123.0	86.4
0°-40°	1238.1	95.3
0°-60°	1285.3	98.9
0°-90°	1299.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1299.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3457	
5°	3278	295
15°	1928	525
25°	638	303
35°	174	115
45°	43	35
55°	12	12
65°	9	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1276435  
CATALOG NUMBER: P3AS17R309835DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3456.8
1°	3454.3
2°	3433.5
3°	3394.2
4°	3345.1
5°	3277.6
6°	3191.7
7°	3096.0
8°	2989.3
9°	2861.6
10°	2725.4
11°	2578.2
12°	2422.3
13°	2259.1
14°	2093.5
15°	1927.8
17.5°	1520.4
20°	1163.3
22.5°	862.7
25°	638.1
27.5°	463.9
30°	338.7
32.5°	244.2
35°	174.3
37.5°	121.5
40°	85.9
42.5°	60.1
45°	42.9
47.5°	29.5
50°	20.9
52.5°	14.7
55°	12.3
57.5°	11.0
60°	9.8
62.5°	8.6
65°	8.6
67.5°	7.4
70°	6.1
72.5°	4.9
75°	3.7
77.5°	3.7
80°	2.5
82.5°	2.5
85°	1.2
87.5°	0.0



TEST NUMBER: P1276435  
CATALOG NUMBER: P3AS17R309835DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):



(END OF REPORT)