

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276467

Luminaire Tested: P3AS17R359835DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359835DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 486.0 lumens
Efficiency: N/A
Efficacy: 23.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276467
CATALOG NUMBER: P3AS17R359835DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1276467
 CATALOG NUMBER: P3AS17R359835DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111022
5°	108672
10°	101757
15°	91351
20°	79457
25°	67722
30°	56718
35°	45186
40°	32661
45°	20684
50°	11258
55°	7799
60°	7368
65°	6849
70°	6540
75°	5592
80°	5304
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20684 cd/sqm



TEST NUMBER: P1276467
 CATALOG NUMBER: P3AS17R359835DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.9	9.5
10°-20°	112.0	23.0
20°-30°	128.3	26.4
30°-40°	104.7	21.5
40°-50°	52.8	10.9
50°-60°	19.6	4.0
60°-70°	13.1	2.7
70°-80°	7.3	1.5
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.2	58.9
0°-40°	391.0	80.4
0°-60°	463.3	95.3
0°-90°	486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	486.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	506	
5°	494	46
15°	402	112
25°	280	128
35°	169	105
45°	67	53
55°	20	20
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1276467
CATALOG NUMBER: P3AS17R359835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	506.3
1°	505.7
2°	504.5
3°	502.1
4°	498.5
5°	493.7
6°	487.7
7°	481.7
8°	473.8
9°	466.0
10°	457.0
11°	447.4
12°	437.2
13°	425.8
14°	413.8
15°	402.4
17.5°	371.8
20°	340.5
22.5°	308.7
25°	279.9
27.5°	251.6
30°	224.0
32.5°	196.4
35°	168.8
37.5°	141.1
40°	114.1
42.5°	88.9
45°	66.7
47.5°	48.0
50°	33.0
52.5°	24.0
55°	20.4
57.5°	18.6
60°	16.8
62.5°	15.0
65°	13.2
67.5°	11.4
70°	10.2
72.5°	8.4
75°	6.6
77.5°	5.4
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2



TEST NUMBER: P1276467
CATALOG NUMBER: P3AS17R359835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)