

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275426

Luminaire Tested: P3AS05R359835DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359835DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 199.0 lumens
Efficiency: N/A
Efficacy: 27.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275426

CATALOG NUMBER: P3AS05R359835DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1275426

CATALOG NUMBER: P3AS05R359835DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100365
5°	96456
10°	84033
15°	64382
20°	43077
25°	26058
30°	14964
35°	8352
40°	4437
45°	2295
50°	1092
55°	879
60°	833
65°	675
70°	705
75°	678
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2295 cd/sqm

TEST NUMBER: P1275426

CATALOG NUMBER: P3AS05R359835DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.9	20.0
10°-20°	77.3	38.8
20°-30°	50.6	25.4
30°-40°	20.5	10.3
40°-50°	6.2	3.1
50°-60°	2.1	1.1
60°-70°	1.4	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.7	84.3
0°-40°	188.2	94.6
0°-60°	196.5	98.7
0°-90°	199.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	199.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	458	
5°	438	40
15°	284	77
25°	108	51
35°	31	21
45°	7	6
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275426

CATALOG NUMBER: P3AS05R359835DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	457.7
1°	457.0
2°	454.9
3°	450.7
4°	445.8
5°	438.2
6°	428.7
7°	418.1
8°	406.2
9°	392.6
10°	377.4
11°	360.6
12°	343.0
13°	323.3
14°	304.6
15°	283.6
17.5°	232.6
20°	184.6
22.5°	142.0
25°	107.7
27.5°	80.3
30°	59.1
32.5°	43.3
35°	31.2
37.5°	22.1
40°	15.5
42.5°	10.8
45°	7.4
47.5°	4.9
50°	3.2
52.5°	2.5
55°	2.3
57.5°	2.1
60°	1.9
62.5°	1.7
65°	1.3
67.5°	1.1
70°	1.1
72.5°	0.9
75°	0.8
77.5°	0.6
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1275426
CATALOG NUMBER: P3AS05R359835DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)