

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275474

Luminaire Tested: P3AS05R409835DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409835DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 450.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275474

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1275474

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199129
5°	193330
10°	175437
15°	144950
20°	104542
25°	64673
30°	35018
35°	18096
40°	9847
45°	5520
50°	2763
55°	2064
60°	1842
65°	1816
70°	1731
75°	1610
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5520 cd/sqm

TEST NUMBER: P1275474

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	18.0
10°-20°	173.9	38.6
20°-30°	124.1	27.6
30°-40°	45.7	10.1
40°-50°	14.4	3.2
50°-60°	5.0	1.1
60°-70°	3.5	0.8
70°-80°	2.0	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.9	84.2
0°-40°	424.6	94.3
0°-60°	443.9	98.7
0°-90°	450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	450.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	908	
5°	878	81
15°	638	174
25°	267	124
35°	68	46
45°	18	14
55°	5	5
65°	4	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1275474

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	908.1
2.5°	901.1
5°	878.3
7.5°	840.5
10°	787.9
12.5°	721.1
15°	638.5
17.5°	545.8
20°	448.0
22.5°	351.9
25°	267.3
27.5°	196.2
30°	138.3
32.5°	96.9
35°	67.6
37.5°	47.9
40°	34.4
42.5°	24.7
45°	17.8
47.5°	12.0
50°	8.1
52.5°	5.8
55°	5.4
57.5°	5.0
60°	4.2
62.5°	3.9
65°	3.5
67.5°	3.1
70°	2.7
72.5°	2.3
75°	1.9
77.5°	1.5
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)