

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276518

Luminaire Tested: P3AS17R459835DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276518
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459835DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 672.0 lumens
Efficiency: N/A
Efficacy: 32.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276518

CATALOG NUMBER: P3AS17R459835DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276518

CATALOG NUMBER: P3AS17R459835DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252370
5°	246444
10°	226538
15°	191965
20°	148926
25°	104111
30°	65580
35°	38601
40°	21841
45°	10637
50°	3684
55°	2982
60°	2895
65°	2802
70°	2693
75°	2542
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10637 cd/sqm

TEST NUMBER: P1276518

CATALOG NUMBER: P3AS17R459835DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	15.4
10°-20°	232.2	34.6
20°-30°	197.2	29.3
30°-40°	94.1	14.0
40°-50°	28.3	4.2
50°-60°	7.2	1.1
60°-70°	5.3	0.8
70°-80°	3.2	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.0	79.3
0°-40°	627.1	93.3
0°-60°	662.6	98.6
0°-90°	672.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	672.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1151	
5°	1120	104
15°	846	232
25°	430	197
35°	144	94
45°	34	28
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1276518

CATALOG NUMBER: P3AS17R459835DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1150.9
2.5°	1143.6
5°	1119.6
7.5°	1078.1
10°	1017.4
12.5°	936.9
15°	845.6
17.5°	744.0
20°	638.2
22.5°	530.7
25°	430.3
27.5°	338.9
30°	259.0
32.5°	194.7
35°	144.2
37.5°	106.4
40°	76.3
42.5°	52.9
45°	34.3
47.5°	19.2
50°	10.8
52.5°	8.4
55°	7.8
57.5°	7.2
60°	6.6
62.5°	6.0
65°	5.4
67.5°	4.8
70°	4.2
72.5°	3.6
75°	3.0
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)