

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275475

Luminaire Tested: P3AS05R409835DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409835DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 284.0 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275475

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1275475

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88436
5°	86639
10°	80671
15°	70307
20°	56658
25°	42462
30°	29853
35°	19568
40°	11851
45°	7071
50°	4230
55°	3403
60°	3070
65°	2594
70°	2500
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7071 cd/sqm

TEST NUMBER: P1275475

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.6	12.9
10°-20°	85.3	30.0
20°-30°	80.4	28.3
30°-40°	46.5	16.4
40°-50°	18.5	6.5
50°-60°	8.2	2.9
60°-70°	5.1	1.8
70°-80°	2.6	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.2	71.2
0°-40°	248.7	87.6
0°-60°	275.5	97.0
0°-90°	284.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	284.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	403	
5°	394	37
15°	310	85
25°	176	80
35°	73	46
45°	23	19
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1275475

CATALOG NUMBER: P3AS05R409835DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	403.3
2.5°	401.0
5°	393.6
7.5°	380.1
10°	362.3
12.5°	338.3
15°	309.7
17.5°	277.6
20°	242.8
22.5°	208.0
25°	175.5
27.5°	145.4
30°	117.9
32.5°	94.0
35°	73.1
37.5°	55.3
40°	41.4
42.5°	30.9
45°	22.8
47.5°	16.6
50°	12.4
52.5°	10.1
55°	8.9
57.5°	8.1
60°	7.0
62.5°	5.8
65°	5.0
67.5°	4.3
70°	3.9
72.5°	3.1
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)